

ABB BALDOR RELIANCE III

Customer information packet

VP3411-14

.18/.25HP, 1750RPM, DC, D71C, 3410P, TEFC, F2

Class - None

Division -

Specifications

Armature Voltage	180 V
Base Speed	1750 rpm
Enclosure	TEFC
Frame	D71C
Frame Material	Steel
Haz Area Class and Group	None
Output Power	0.250 HP
Agency Approvals	CE CSA UR
Ambient Temperature	40 °C
Armature Current	1.4 a
Armature Inertia	3.902 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Frame Prefix	D
Heater Indicator	No Heater
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 14 AWG, A
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Mounting Arrangement	B34
Overall Length	12.27 IN
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Service Factor	1.00
Shaft Diameter	0.552 IN
Shaft Extension Location	Pulley End

Part Detail

Revision	AD
Type	DC
Mech. spec.	34-6242
Base	
Status	PRD/A
Elec. spec.	34WG4169
Layout	34LY6242
Eff. date	10-25-2024
CD Diagram	CD0194
Poles	00
Leads	2#14 A Y
Proprietary	False
Created date	01-01-0001

Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Nameplate

NP1049L				
CAT.NO.	VP3411-14			
SPEC.	34-6242-4169			
KW/HP	.18/.25 TE		I.P.	54
RPM	1750 TE			
IEC FRAME	D71C	TYPE	3410P	
ARM V	180		ARM A	1.4
FLD V			FLD A	
INSUL	F	AMB.	40	
DUTY	CONT		SUPPLY	1.5
BRG/DE	6203	BRG/ODE		6203
BRUSHES	2/BP5000AW14			
			BLANK	
SER.				
BLANK				
APRV-CE		APRV-CSA		APRV-UL

Accessories

Part number	Description	Multiplier
TK3400	TACHO MOUNTING KIT FOR TK3400	A8
TK3400-HPU	HPU10 MOUNTING KIT 34P/35P TEFC	

DC Motor Performance Data

Record # 431

Typical performance - not guaranteed values

Winding: 34WG4169-R001		Type: 3410P	Enclosure: TEFC
Nameplate Data		General Characteristics	
Rated Output (KW)	0.19		
R.P.M.	1750		
Armature Volts	180		
Armature Amps	1.4		
Field Volts			
Field Amps			
Rating - Duty	40C AMB-CONT		
Form Factor	1.5		

Load Characteristics at 180 Armature Volts

Load Point	1	2	3	4	5	6	7
Armature Amps	0.128	0.388	0.648	0.908	1.168	1.428	1.688
R.P.M.	1744	1712	1681	1649	1617	1586	1554
Torque (LB-FT)	0	0.1875	0.375	0.5625	0.75	0.9375	1.125


ABB Motors and Mechanical Inc.

WINDING # 34WG4169


Typical performance - not guaranteed values.

0.19 KW DC 1750 RPM 180 V 3410P

ENCL: TEFC DUTY: CONT CL: F



34LY6242



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: LOAD TO SOLIDWORKS - REV N

REV: P VERSION: 02 REVISED: 11:41:34 12/22/2022 TDR: 000001201165

34LY6242

MODEL NO. 34LY6242

BY: ENFRAJ0


REF: -

BALDOR - RELIANCE®

STD HORZ MODEL 34 PM TEFC IEC D71C-B14 2 POLE W/M.F.T.K.

34LY6242

CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -

REV: E

ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."

CD0194

SCALE: -

BY: CK

REVISED: 07/28/95

FILE: AAA00004503

TDR: 0078737

BALDOR ELECTRIC Co.

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194