

ABB BALDOR RELIANCE III

Customer information packet

VP3428-14

.37KW/.5HP/3000RPM/TEFC/IEC/71C MOTOR

Class - None

Division - Not Applicable

Specifications

Armature Voltage	180 V
Base Speed	3000 rpm
Enclosure	TEFC
Frame	D71C
Haz Area Class and Group	None
Output Power	0.500 HP
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Armature Current	2.5 a
Armature Inertia	6.243 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Frame Prefix	D
Haz Area Division	Not Applicable
Heater Indicator	No Heater
Insulation Class	F
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Mounting Arrangement	B34
Overall Length	12.27 IN
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Service Factor	1.00
Shaft Diameter	0.551 IN
Shaft Extension Location	Pulley End

Part Detail

Revision	Z
Type	DC
Mech. spec.	34-6242
Base	
Status	PRD/A
Elec. spec.	34WGZ132
Layout	34LY6242
Eff. date	10-25-2024
CD Diagram	CD0194
Poles	00
Leads	
Proprietary	False
Created date	01-01-0001

Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Nameplate

NP1049L					
CAT.NO.	VP3428-14				
SPEC.	34-6242Z132				
KW/HP	.37/.5 TE			I.P.	44
RPM	3000 1/MIN				
IEC FRAME	D71C	TYPE		3416P	
ARM V	180			ARM A	2.5
FLD V				FLD A	
INSUL	F	AMB.		40	
DUTY	CONT			SUPPLY	1.5
BRG/DE	6203	BRG/ODE			6203
BRUSHES	2/BP5000AW14				
				BLANK	KG15 IC411
SER.					
BLANK	IEC60034-1;-5				
APRV-CE	Y	APRV-CSA	Y	APRV-UL	Y

Accessories

Part number	Description	Multiplier
TK3400	TACHO MOUNTING KIT FOR TK3400	A8
TK3400-HPU	HPU10 MOUNTING KIT 34P/35P TEFC	

DC Motor Performance Data

Record # 2640

Typical performance - not guaranteed values

Winding: 34WGZ132-R001		Type: 3416P	Enclosure: TEFC
Nameplate Data		General Characteristics	
Rated Output (HP)	0.5	Armature Resistance @ 25°C	2.069 Ω
R.P.M.	3000		
Armature Volts	180	Voltage Constant	58.56 v/krpm
Armature Amps	2.5		
Field Volts			
Field Amps		Armature Inertia	6.2432 LI ²
Rating - Duty	40C AMB-CONT		
Form Factor	1.5		

Load Characteristics at 180 Armature Volts

Load Point	1	2	3	4	5	6
Armature Amps	0.3	1.6	2.2	2.9	3.5	4.2
R.P.M.	3262	3177	3144	3099	3064	3016
Torque (LB-FT)	0	0.516	0.752	1.01	1.246	1.504


ABB Motors and Mechanical Inc.

WINDING # 34WGZ132


Typical performance - not guaranteed values.

0.5 HP DC 3000 RPM 180 V 3416P

ENCL: TEFC DUTY: CONT CL: F



34LY6242



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: LOAD TO SOLIDWORKS - REV N

REV: P

VERSION: 02

REVISED: 11:41:34 12/22/2022

TDR: 000001201165

BALDOR - RELIANCE®

34LY6242

MODEL NO. 34LY6242


REF: -

BY: ENFRAJ0

STD HORZ MODEL 34 PM TEFC IEC D71C-B14 2 POLE W/M.F.T.K.

34LY6242

CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -			
REV:	E	ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."	
CD0194		SCALE: -	BY: CK
		FILE: AAA00004503	TDR: 0078737

BALDOR ELECTRIC Co.

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194