Customer information packet

VSPM3314T

15HP, 3515RPM, 3PH, 60HZ, 215TC, 3756M, OPSB, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/14/2026 11:39:34 PM

Specifications

Enclosure	OPSB
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	WEEE
	NEMA PREMIUM 4
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	17.000 A @ 460.0 V
	34.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	17.0 a
Insulation Class	F

Part Detail

Revision	B
Type	AC
Mech. spec.	37T654
Base	
Status	PRD/A
Elec. spec.	37WGR601
Layout	37LYT654
Eff. date	11-19-2025
CD Diagram	CD0180
Poles	02
Leads	9#14
Proprietary	False
Created date	11-29-2023

Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3756M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	19.69 IN
Power Factor	88
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3515 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4423A01A01L												
CAT #	VSPM3314T			**WGT**	187	**LBS**						
SPEC	37T654R601			**ENCL**	OPSB							
SER #				**CC**	010A	**IP**	23					
HP	15		**MAG CUR**	11.6/5.8								
VOLTS	230/460				**NEMA NOM. EFF**	92.4						
AMPS	34/17			**PF**	88							
RATING	40C AMB-CONT											
RPM	3515			**MAX RPM**	5400							
FRAME	215TC	**HZ**	60	**CODE**	K	**CLASS**	F					
SER.F.	1.15	**SF AMP**	39/19.5		**PH**	3	**DES**	A				
DE	6307		**ODE**	6206								
LUBRICATION	POLYREX EM											
ID LOGO	**INVERTER TYPE**		**VPWM**		**CHP**	60	**TO**	90	1.5:1			
ID LOGO	**WK2**	0.51	**CT**	6	**TO**	60	10:1					
ID LOGO	**SL HZ**	1.4	**VT**	3	**TO**	60	20:1					
					QR							
YR												


AC Induction Motor Performance Data
Record # 100931
Typical performance - not guaranteed values


Winding: 37WGR601-R005	**Type:** 3756M	**Enclosure:** ODP

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			15	**Full Load Torque**	22.09 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			34/17	**Breakdown Torque**	112 LB-FT
R.P.M.			3515	**Pull-up Torque**	43.2 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	62 LB-FT
NEMA Design Code	A	**KVA Code**	K	**Starting Current**	161 A
Service Factor (S.F.)			1.15	**No-load Current**	5.75 A
NEMA Nom. Eff.	92.4	**Power Factor**	88	**Line-line Res. @ 25ºC**	0.406 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	40°C
S.F. Amps			39/19.5	**Temp. Rise @ S.F. Load**	49°C
				Locked-rotor Power Factor	29.9
				Rotor inertia	0.51 lb-ft²


Load Characteristics 460 V, 60 Hz, 15 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	53	76	85	88	90	90	89
Efficiency	89.4	92.8	93.2	92.7	91.9	90.8	92.2
Speed	3580	3561	3539	3516	3491	3465	3501
Line amperes	6.81	9.54	13.1	16.95	20.9	25.31	19.3



ABB Motors and Mechanical Inc.
WINDING # 37WGR601
Typical performance - not guaranteed values.
15 HP 3 PH 60 HZ 3515 RPM 460 V 3756M
TORQUES(LB-FT): PO=112 PU=43.2 LR=62 LRA=161
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF
%PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (15 HP)
11/14/2026 ACPERF, record # 100931


37LYT654
(717-735) = 17.07
(736-744) = 18.19
(745-750) = 18.94
(751-756) = 19.69
3.44
3.12
.26
.31 KEY
2.25 LONG
8.500
8.497
Ø1.3750
1.3745
9.06
Ø9.57
7.90
45°
45°
LIFTING LUG
(1 EA. END)
4 HOLES
.50-13 TAP
Ø7.25 B.C.
LEAD HOLE
Ø1.38
6.73
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW
REV: - VERSION: 00 REVISED: 07:27:55 01/04/2024 TDR: 000001222999
MODEL NO. 37LYT654 REF: -
BY: USALMAZ B
BALDOR
VERT 213-5TC OPSB 37M, 'A64 NP
37LYT654

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1