



---

# Customer information packet

## VSPM3708T

5HP, 1165RPM, 3PH, 60HZ, 215TC, 3754M, TEFC, F1

Class - None

Division - Not Applicable

## Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA_PREMIUM WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	14.800 A @ 230.0 V 7.400 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	7.4 a

## Part detail

Revision	-
Type	AC
Mech. spec.	37T656
Base	
Status	PRD/A
Elec. spec.	37WGS405
Layout	37LYT656
Eff. date	08-09-2024
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	11-29-2023

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3754M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	21.25 IN
Power Factor	70
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

NP4423A01A01L									
<b>CAT #</b>	VSPM3708T			<b>WGT</b>	149	<b>LBS</b>			
<b>SPEC</b>	37T656S405			<b>ENCL</b>	TEFC				
<b>SER #</b>				<b>CC</b>	010A	<b>IP</b>	54		
<b>HP</b>	5	<b>MAG CUR</b>		8/4					
<b>VOLTS</b>	230/460			<b>NEMA NOM. EFF</b>		90.2			
<b>AMPS</b>	14.8/7.4			<b>PF</b>	70				
<b>RATING</b>	40C AMB-CONT								
<b>RPM</b>	1165			<b>MAX RPM</b>		1800			
<b>FRAME</b>	215TC	<b>HZ</b>	60	<b>CODE</b>	L	<b>CLASS</b>	F		
<b>SER.F.</b>	1.15	<b>SF AMP</b>	16.6/8.3		<b>PH</b>	3	<b>DES</b>	A	
<b>DE</b>	6307		<b>ODE</b>		6206				
<b>LUBRICATION</b>	POLYREX EM								
<b>ID LOGO</b>	<b>INVERTER TYPE</b>		<b>VPWM</b>	<b>CHP</b>	60	<b>TO</b>	90	1.5:1	
<b>ID LOGO</b>	<b>WK2</b>	1.34	<b>CT</b>	6	<b>TO</b>	60	10:1		
<b>ID LOGO</b>	<b>SL HZ</b>	1.75	<b>VT</b>	3	<b>TO</b>	60	20:1		
				<b>QR</b>					
<b>YR</b>									

**AC Induction Motor Performance Data**

Record # 100916

Typical performance - not guaranteed values

<b>Winding: 37WGS405-R005</b>		<b>Type: 3754M</b>		<b>Enclosure: TEFC</b>	
<b>Nameplate Data</b>			<b>460 V, 60 Hz: High Voltage Connection</b>		
<b>Rated Output (HP)</b>	5		<b>Full Load Torque</b>	22.5 LB-FT	
<b>Volts</b>	230/460		<b>Start Configuration</b>	direct on line	
<b>Full Load Amps</b>	14.8/7.4		<b>Breakdown Torque</b>	86.3 LB-FT	
<b>R.P.M.</b>	1165		<b>Pull-up Torque</b>	46.4 LB-FT	
<b>Hz</b>	<b>60 Phase</b>	3	<b>Locked-rotor Torque</b>	58.5 LB-FT	
<b>NEMA Design Code</b>	<b>A KVA Code</b>	L	<b>Starting Current</b>	57.8 A	
<b>Service Factor (S.F.)</b>	1.15		<b>No-load Current</b>	4.01 A	
<b>NEMA Nom. Eff.</b>	<b>90.2 Power Factor</b>	70	<b>Line-line Res. @ 25°C</b>	1.4 Ω	
<b>Rating - Duty</b>	40C AMB-CONT		<b>Temp. Rise @ Rated Load</b>	55°C	
<b>S.F. Amps</b>	16.6/8.3		<b>Temp. Rise @ S.F. Load</b>	66°C	
			<b>Locked-rotor Power Factor</b>	21.4	
			<b>Rotor inertia</b>	1.34 lb-ft <sup>2</sup>	

**Load Characteristics 460 V, 60 Hz, 5 HP**

<b>% of Rated Load</b>	<b>25</b>	<b>50</b>	<b>75</b>	<b>100</b>	<b>125</b>	<b>150</b>	<b>S.F.</b>
<b>Power Factor</b>	31	51	63	70	73	76	72
<b>Efficiency</b>	85.5	89.9	91	90.3	89.7	88.1	89.9
<b>Speed</b>	1191	1184	1175	1166	1156	1145	1160
<b>Line amperes</b>	4.32	5.12	6.16	7.44	8.88	10.5	8.3


ABB Motors and Mechanical Inc.

WINDING # 37WGS405


Typical performance - not guaranteed values.

5 HP 3 PH 60 HZ 1165 RPM 460 V 3754M


TORQUES (LB-FT): PO=86.3 PU=46.4 LR=58.5 LRA=57.8




4/18/2025 ACPERF, record # 100916



CD0005




LOW VOLTAGE  
(2Y)



LINE

HIGH VOLTAGE  
(1Y)



LINE

**NOTES:**

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 9 LEADS