

ABB BALDOR RELIANCE III

Customer information packet

VSPM31111

.75HP, 3450RPM, 3PH, 60HZ, 56C, 3424M, ODP, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	ODP
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	WEEE C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.000 A @ 460.0 V 2.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.0 a
Insulation Class	F

Part Detail

Revision	B
Type	AC
Mech. spec.	34B063
Base	
Status	PRD/A
Elec. spec.	34WGW715
Layout	34LYB063
Eff. date	12-30-2024
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	03-06-2024

Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3424M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	11.76 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Page 4 of 8

AC Induction Motor Performance Data

Record # 100844

Typical performance - not guaranteed values

Winding: 34WGW715-R015			Type: 3424M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		.75	Full Load Torque		1.1 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		2/1	Breakdown Torque		5.4 LB-FT		
R.P.M.		3450	Pull-up Torque		4 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		5.2 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		9 A
Service Factor (S.F.)		1.25		No-load Current		0.53 A	
NEMA Nom. Eff.		80	Power Factor	81	Line-line Res. @ 25°C		15 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		30°C	
S.F. Amps		2.4/1.2		Temp. Rise @ S.F. Load		36°C	
				Locked-rotor Power Factor		62.1	
				Rotor inertia		0.0223 lb-ft²	

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	47	66	76	81	84	85	84
Efficiency	62.6	75	79.6	81.3	81.7	81.3	81.7
Speed	3559	3526	3491	3455	3415	3373	3415
Line amperes	0.59	0.7	0.85	1.03	1.22	1.44	1.22

ABB Motors and Mechanical Inc.

WINDING # 34WG715

Typical performance - not guaranteed values.

0.75 HP 3 PH 60 HZ 3450 RPM 460 V 3424M

TORQUES (LB-FT) : PO=5.4 PU=4 LR=5.2 LRA=9





