

ABB BALDOR RELIANCE III

Customer information packet

VSSWDM3541

.75HP, 3450RPM, 3PH, 60HZ, 56C, 3518M, TENV, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Stainless Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.100 A @ 460.0 V 2.200 A @ 230.0 V 2.300 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	AJ
Type	AC
Mech. spec.	35V824
Base	
Status	PRD/A
Elec. spec.	35WGT097
Layout	35LYV824
Eff. date	02-19-2024
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	06-22-2007

High Voltage Full Load Amps	1.1 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3518M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	11.09 IN
Power Factor	80
Product Family	Wash Down All Stainless Steel
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Nameplate

NP1951A01												
CAT.NO.	VSSWDM3541											
SPEC.	35V824T097											
HP	.75											
VOLTS	230/460											
AMP	2.2/1.1											
RPM	3450											
FRAME	56C			HZ		60		PH		3		
SER.F.	1.25	CODE		N	DES	B	CLASS		F			
NEMA-NOM-EFF	80			PF		80						
RATING	40C AMB-CONT											
CC												
DE	6205			ODE		6203						
ENCL	TENV	SN										
	SFA 2.6/1.3											
	10:1CT 20:1VT											

AC Induction Motor Performance Data

Record # 9255

Typical performance - not guaranteed values

Winding: 35WGT097-R001			Type: 3518M		Enclosure: TENV	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.75	Full Load Torque		1.1 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		2.2/1.1	Breakdown Torque		7.6 LB-FT	
R.P.M.		3450	Pull-up Torque		4.1 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque		5.6 LB-FT	
NEMA Design Code		B	KVA Code		N	
Service Factor (S.F.)		1.25	Starting Current		11.7 A	
NEMA Nom. Eff.		80	Power Factor		80	
Rating - Duty		40C AMB-CONT	Line-line Res. @ 25°C		14.8 Ω	
S.F. Amps		2.6/1.3	Temp. Rise @ Rated Load		65°C	
			Temp. Rise @ S.F. Load		77°C	

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	63	73	80	81	80	0
Efficiency	62.6	74.4	78.7	80.4	80.7	80.1	0
Speed	3571	3536	3509	3477	3444	3406	0
Line amperes	0.66	0.76	0.91	1.09	1.29	1.52	1.3

ABB Motors and Mechanical Inc.

WINDING # 35WGT097

Typical performance - not guaranteed values.

0.75 HP 3 PH 60 HZ 3450 RPM 460 V 3518M

TORQUES (LB-FT): PO=7.6 PU=4.1 LR=5.6 LRA=11.7





