

ABB BALDOR RELIANCE III

Customer information packet

VSPM3542

.75HP, 1735RPM, 3PH, 60HZ, 56C, 3436M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	WEEE C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.950 A @ 460.0 V 1.900 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.0 a
Insulation Class	F

Part Detail

Revision	C
Type	AC
Mech. spec.	34N585
Base	
Status	PRD/A
Elec. spec.	34WGR770
Layout	34LYN585
Eff. date	03-06-2025
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	03-07-2024

Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3436M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.72 IN
Power Factor	87
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1735 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Page 4 of 8

AC Induction Motor Performance Data

Record # 100602

Preliminary Data Sheet

Winding: 34WGR770-R001			Type: 3436M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.75	Full Load Torque		2.29 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		1.9/0.95	Breakdown Torque		10.1 LB-FT	
R.P.M.		1735	Pull-up Torque		7.8 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque		8.8 LB-FT	
NEMA Design Code		B	KVA Code		N	
Starting Current				9 A		
Service Factor (S.F.)		1.15	No-load Current		0.49 A	
NEMA Nom. Eff.		84	Power Factor		87	
Line-line Res. @ 25°C				15.4 Ω		
Temp. Rise @ Rated Load				24°C		
Temp. Rise @ S.F. Load				28°C		
Locked-rotor Power Factor				46.4		
Rotor inertia				0.0857 lb-ft²		

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	43	67	80	87	90	92	89
Efficiency	78.1	85.5	86.7	86.5	85.1	83	85.7
Speed	1783	1767	1751	1734	1713	1688	1721
Line amperes	0.53	0.62	0.77	0.94	1.16	1.43	1.07


ABB Motors and Mechanical Inc.

WINDING # 34WGR770

Typical performance - not guaranteed values.


0.75 HP 3 PH 60 HZ 1735 RPM 460 V 3436M

TORQUES (LB-FT): PO=10.1 PU=7.8 LR=8.8 LRA=9



10/18/2026 ACPERF, record # 100602

34LYN585



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: NEW			
REV: -	VERSION: 00	REVISED: 01:20:17 03/05/2024	TDR: 000001227262
34LYN585		MODEL NO. 34LYN585	REF: -
		BY: USALMAZ	

BALDOR - RELIANCE®

VERT 34M NEMA 56C TEFC W/DRAINS (IP54)

34LYN585

