

ABB BALDOR RELIANCE III

Customer information packet

VXL050362A

.33HP, 1160RPM, 1PH, 60HZ, 56C, 3528L, XPFC, F1

Class - CLI GP D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.330 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	UL CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.000 A @ 230.0 V 8.000 A @ 115.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	47.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T4
Heater Indicator	No Heater
High Voltage Full Load Amps	4.0 a

Part Detail

Revision	K
Type	AC
Mech. spec.	35E371
Base	
Status	PRD/A
Elec. spec.	35WGG244
Layout	35LYE371
Eff. date	06-16-2026
CD Diagram	CD0008
Poles	06
Leads	6#18,1#14 #4TH
Proprietary	False
Created date	02-23-2023

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	R
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X3528L
Mounting Arrangement	F1
Number of Poles	6
Overall Length	15.18 IN
Power Factor	47
Product Family	Hazardous Location Motor
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1170 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Do Not Use Eve-Not Valid
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	SB
Winding Thermal 2	None

Nameplate

NP0016XPSL									
NO.		CC							
SER. #									
SPEC	35E371G244								
CAT.NO.	VXL050362A								
H.P.	.33	T. CODE	T4						
VOLTS	115/230								
AMPS	8/4								
R.P.M.	1170								
HZ	60	PH	1	CLASS	F				
SER.F.	1.00	DES	L	CODE	R				
RATING	40C AMB-CONT								
FRAME	56C	NEMA NOM. EFF	47						
	PF	47							
BLANK									

AC Induction Motor Performance Data

Record # 116898

Typical performance - not guaranteed values

Winding: 35WGG244-R004			Type: 3528L		Enclosure: XPFC			
Nameplate Data			230 V, 60 Hz: High Voltage Connection					
Rated Output (HP)		.33	Full Load Torque		1.5 LB-FT			
Volts		115/230	Start Configuration		direct on line			
Full Load Amps		8/4	Breakdown Torque		6.3 LB-FT			
R.P.M.		1170	Pull-up Torque		4.8 LB-FT			
Hz	60	Phase	1	Locked-rotor Torque		7 LB-FT		
NEMA Design Code		L	KVA Code	R	Starting Current		21.9 A	
Service Factor (S.F.)			1	No-load Current		3.05 A		
NEMA Nom. Eff.		47	Power Factor		47	Line-line Res. @ 25°C		1.21 Ω A Ph 3.34 Ω B Ph
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		65°C		
				Locked-rotor Power Factor		92.9		
				Rotor inertia		0.203 lb-ft²		

Load Characteristics 230 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	30	41	51	58	64	68
Efficiency	30.5	40.5	45.1	47.2	47.6	47.1
Speed	1193	1187	1180	1172	1162	1150
Line amperes	3.12	3.29	3.58	3.95	4.45	5.07


ABB Motors and Mechanical Inc.


WINDING # 35WGG244

Typical performance - not guaranteed values.


0.33 HP 1 PH 60 HZ 1170 RPM 230 V 3528L

TORQUES (LB-FT) : PO=6.3 PU=4.8 LR=7 LRA=21.9





CD0008



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J,8
LOW STD	1,3,8	4	—	2,J,5
LOW OPP	1,3,5	4	—	2,J,8

- NOTES:
1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
 2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
 3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REMOVE 2-TERMINAL THERMAL DETAIL, SEE CD0008A02		
REV. LTR: F	VERSION: 01	TDR: 000000360649
800000	FILE: \AAA\00007\408	REVISED: 10:56:54 04/18/2005
	MTL: —	BY: ENJOEPO

BALDOR ELECTRIC Co.

TYPE L, DV, REV, THERMAL, 7 LEADS

CD0008