ABB BALDOR RELIANCE

Customer information packet

VUHL3519

1/.75KWHP, 1745RPM, 1PH, 60HZ, 56C, 3526LC, TE
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/18/2026 4:38:34 PM

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	208.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	C UR US
	CE
	CURUS
	UKCA
	WEEE
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.800 A @ 115.0 V
	5.100 A @ 208.0 V
	4.900 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	78.0 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	D
Type	AC
Mech. spec.	35E022
Base	
Status	PRD/A
Elec. spec.	35WGG590
Layout	35LYE022
Eff. date	09-17-2025
CD Diagram	CD0055
Poles	04
Leads	6#18
Proprietary	False
Created date	10-09-2023

Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	4.9 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.23 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1745 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP1372L										
CAT.NO.	VUHL3519									
SPEC.	35E022G590									
HP	1/.75KW									
VOLTS	115/208-230									
AMP	9.8/5.1-4.9									
R.P.M. (1/MIN)	1745									
FRAME	56C	**HZ**	60	**PH**	1					
SER.F.	1.15	**CODE**	L	**DES**	L	**CL**	F			
NEMA-NOM-EFF	78	**PF**	90							
RATING	40C AMB-S1 CONT									
CC			IP44 IC411 27KG							
DE	6205	**ODE**	6203							
ENCL	TEFC	**SN**								
	IE2-60HZ 78(75%),73(50%)									


AC Induction Motor Performance Data
Record # 101476
Typical performance - not guaranteed values

Winding: 35WGG590-R001	**Type:** 3526LC	**Enclosure:** TEFC

Nameplate Data				**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	3.061 LB-FT
Volts			115/208-230	**Start Configuration**	direct on line
Full Load Amps			9.8/5.1-4.9	**Breakdown Torque**	10.6 LB-FT
R.P.M.			1745	**Pull-up Torque**	7.64 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	11.7 LB-FT
NEMA Design Code	L	**KVA Code**	L	**Starting Current**	40 A
Service Factor (S.F.)			1.15	**No-load Current**	2.7 A
NEMA Nom. Eff.	78	**Power Factor**	90	**Line-line Res. @ 25ºC**	2.6387 Ω A Ph 1.4489 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	53°C
S.F. Amps			11/5.9-5.5	**Temp. Rise @ S.F. Load**	62°C

Load Characteristics 230 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	52	69	79	86	89	91	88
Efficiency	58.6	73.2	78.2	79.7	79.1	77.2	79.3
Speed	1784.6	1772.8	1760	1745.1	1727.5	1707.7	1735
Line amperes	2.86	3.32	4.01	4.84	5.83	7.01	5.43


ABB Motors and Mechanical Inc.
WINDING # 35WGG590
1 HP 1 PH 60 HZ 1745 RPM 230 V 3526LC
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=10.6 PU=7.64 LR=11.7 LRA=40
TORQUE
RPM
WATTS
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
WATTS
AMPS
PERCENT OF RATED OUTPUT (1 HP)
11/18/2026 ACPERF, record # 101476

AC Induction Motor Performance Data
Record # 101477
Typical performance - not guaranteed values

Winding: 35WGG590-R001	**Type:** 3526LC	**Enclosure:** TEFC

Nameplate Data				**208 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1	**Full Load Torque**	3.056 LB-FT
Volts			115/208-230	**Start Configuration**	direct on line
Full Load Amps			9.8/5.1-4.9	**Breakdown Torque**	6.76 LB-FT
R.P.M.			1745	**Pull-up Torque**	5.4 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	7.69 LB-FT
NEMA Design Code	L	**KVA Code**	L	**Starting Current**	35.1 A
Service Factor (S.F.)			1.15	**No-load Current**	2.02 A
NEMA Nom. Eff.	78	**Power Factor**	90	**Line-line Res. @ 25ºC**	2.6174 Ω A Ph 1.4374 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	50°C
S.F. Amps			11/5.9-5.5	**Temp. Rise @ S.F. Load**	63°C

Load Characteristics 208 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	62	78	86	90	92	93	91
Efficiency	63.7	76.2	79.3	79.1	76.4	71.7	77.5
Speed	1782.4	1767.7	1751.1	1730.8	1705.4	1670.8	1716
Line amperes	2.34	3.04	3.95	5.04	6.38	8.09	5.84


ABB Motors and Mechanical Inc.

WINDING # 35WGG590


1 HP 1 PH 60 HZ 1745 RPM 208 V 3526LC

TORQUES(LB-FT): PO=6.76 PU=5.4 LR=7.69 LRA=35.1


Typical performance - not guaranteed values.



11/18/2026 ACPERF, record # 101477


35LYE022
510-528 = 13.23
529-535 = 14.10
536-546 = 15.48
2.06
1.88
.13
.19 KEY
1.38 LONG
Ø7.19
NAMEPLATE
Ø6.49
Ø4.500
4.497
Ø.6250
.6245
3.75
6.61
5.75
4.18
45°
45°
5.55
THERMAL
(WHEN
REQ'D)
LEAD HOLE
Ø.88
4.63
4 HOLES
.38-16 TAP
ON Ø5.88 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD THERMAL DIMS AND THERMAL WHEN REQUIRED NOTE
REV: S
VERSION: 09
REVISED: 02:19:48 03/13/2023
TDR: 000001205626
MODEL NO. 35LYE022
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD VERT 56C TEFC 35LC
SH 1 of 1
35LYE022

CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
CD0055		FILE: AAA00007414	MDL: –
		MTL: –	TYPE LC, DV, REV, 6 LEADS