

ABB BALDOR RELIANCE III

Customer information packet

VWDM3457

.33HP, 3450RPM, 3PH, 60HZ, 56C, 3410M, TENV, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.600 A @ 208.0 V 1.400 A @ 230.0 V .700 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	B
Type	AC
Mech. spec.	34J664
Base	
Status	INA/A
Elec. spec.	34WGY170
Layout	34LYJ664
Eff. date	04-03-2018
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	12-12-2013

Heater Indicator	No Heater
High Voltage Full Load Amps	0.7 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	P
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3410M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	10.26 IN
Power Factor	64
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1496L											
CAT.NO.	VWDM3457										
SPEC.	34J664Y170G2										
HP	.33										
VOLTS	208-230/460										
AMP	1.6-1.4/.7										
RPM	3450										
FRAME	56C		HZ		60		PH		3		
SER.F.	1.25	CODE		P	DES	B	CLASS		F		
NEMA-NOM-EFF	72	PF		64							
RATING	40C AMB-CONT										
CC											
DE	6203		ODE		6203						
ENCL	TENV	SN									
	SFA 1.7-1.5/.75										

AC Induction Motor Performance Data

Record # 44203

Typical performance - not guaranteed values

Winding: 34WGY170-R014			Type: 3410M		Enclosure: TENV	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.33	Full Load Torque		0.5 LB-FT	
Volts		208-230/460	Start Configuration		direct on line	
Full Load Amps		1.6-1.4/.7	Breakdown Torque		3.4 LB-FT	
R.P.M.		3450	Pull-up Torque		2.4 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque		2.6 LB-FT	
NEMA Design Code		B KVA Code	Starting Current		5.8 A	
Service Factor (S.F.)		1.15	No-load Current		0.56 A	
NEMA Nom. Eff.		72 Power Factor	Line-line Res. @ 25°C		31.3 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		57°C	
S.F. Amps		1.7-1.5/.75	Temp. Rise @ S.F. Load		62°C	
			Locked-rotor Power Factor		71	
			Rotor inertia		0.0093 LB-FT2	

Load Characteristics 460 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	29	43	53	64	70	78	73
Efficiency	43.6	61.9	68.2	72.8	74.4	75.8	75
Speed	3569	3544	3526	3497	3477	3444	3464
Line amperes	0.57	0.6	0.63	0.68	0.71	0.79	0.742


ABB Motors and Mechanical Inc.


WINDING # 34WGY170

Typical performance - not guaranteed values.




0.33 HP 3 PH 60 HZ 3450 RPM 460 V 3410M

TORQUES (LB-FT) : PO=3.4 PU=2.4 LR=2.6 LRA=5.8





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005