ABB BALDOR RELIANCE

Customer information packet

VWDM3457

.33HP, 3450RPM, 3PH, 60HZ, 56C, 3410M, TENV, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/19/2026 7:52:30 AM

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.600 A @ 208.0 V
	1.400 A @ 230.0 V
	.700 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	B
Type	AC
Mech. spec.	34J664
Base	
Status	INA/A
Elec. spec.	34WGY170
Layout	34LYJ664
Eff. date	04-03-2018
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	12-12-2013

Heater Indicator	No Heater
High Voltage Full Load Amps	0.7 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	P
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3410M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	10.26 IN
Power Factor	64
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1496L									
CAT.NO.	VWDM3457								
SPEC.	34J664Y170G2								
HP	.33								
VOLTS	208-230/460								
AMP	1.6-1.4/.7								
RPM	3450								
FRAME	56C	**HZ**	60			**PH**	3		
SER.F.	1.25	**CODE**	P	**DES**	B	**CLASS**	F		
NEMA-NOM-EFF	72	**PF**	64						
RATING	40C AMB-CONT								
CC									
DE	6203	**ODE**	6203						
ENCL	TENV	**SN**							
	SFA 1.7-1.5/.75								

AC Induction Motor Performance Data
Record # 44203
Typical performance - not guaranteed values

Winding: 34WGY170-R014	**Type:** 3410M	**Enclosure:** TENV

Nameplate Data			**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)		.33	**Full Load Torque**	0.5 LB-FT
Volts		208-230/460	**Start Configuration**	direct on line
Full Load Amps		1.6-1.4/.7	**Breakdown Torque**	3.4 LB-FT
R.P.M.		3450	**Pull-up Torque**	2.4 LB-FT
Hz	60 **Phase**	3	**Locked-rotor Torque**	2.6 LB-FT
NEMA Design Code	B **KVA Code**	P	**Starting Current**	5.8 A
Service Factor (S.F.)		1.15	**No-load Current**	0.56 A
NEMA Nom. Eff.	72 **Power Factor**	64	**Line-line Res. @ 25ºC**	31.3 Ω
Rating - Duty		40C AMB-CONT	**Temp. Rise @ Rated Load**	57°C
S.F. Amps		1.7-1.5/.75	**Temp. Rise @ S.F. Load**	62°C
			Locked-rotor Power Factor	71
			Rotor inertia	0.0093 LB-FT2

Load Characteristics 460 V, 60 Hz, 0.33 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	29	43	53	64	70	78	73
Efficiency	43.6	61.9	68.2	72.8	74.4	75.8	75
Speed	3569	3544	3526	3497	3477	3444	3464
Line amperes	0.57	0.6	0.63	0.68	0.71	0.79	0.742


ABB Motors and Mechanical Inc.

WINDING # 34WGY170


0.33 HP 3 PH 60 HZ 3450 RPM 460 V 3410M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=3.4 PU=2.4 LR=2.6 LRA=5.8



34LYJ664



PULLEY END DETAIL



APPLY COAT OF RED SEALER
TO HOUSING AND UNDER SCREW
HEADS BEFORE PRESSING SEAL
IN WITH LIP OUT

34LYJ664

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.


REV. DESC: UPDATED KOBX & LID		
REV. LTR: B	VERSION: 02	TDR: 000000830766
FILE: \AAA\00103\295	REVISED: 08:30:02 12/13/2013	BY: ENFRAJ0
MTL: –		


BALDOR

VER 34M NEMA 56C TENV WASHDOWN

SH 1 of 1

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS