Customer information packet

VWDM3534

.33HP, 1780RPM, 3PH, 60HZ, 56C, 3512M, TENV, N
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/11/2026 11:15:13 AM

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ
	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.700 A @ 230.0 V
	1.500 A @ 208.0 V
	.850 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	75.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	C
Type	AC
Mech. spec.	35S603
Base	
Status	PRD/A
Elec. spec.	35WGG155
Layout	35LYS603
Eff. date	06-05-2025
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	07-05-2022

High Voltage Full Load Amps	0.9 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	S
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3512M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.05 IN
Power Factor	49
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1496L											
CAT.NO.	VWDM3534										
SPEC.	35S603G155G5										
HP	.33										
VOLTS	208-230/460										
AMP	1.5-1.7/.85										
RPM	1780										
FRAME	56C		**HZ**	60			**PH**	3			
SER.F.	1.25	**CODE**	S	**DES**	B	**CLASS**	F				
NEMA-NOM-EFF	75.5	**PF**	49								
RATING	40C AMB-CONT										
CC											
DE	6205		**ODE**	6203							
ENCL	TENV	**SN**									
	SFA 1.9-1.8/.9										

AC Induction Motor Performance Data
Record # 82222
Typical performance - not guaranteed values

Winding: 35WGG155-R015	**Type:** 3512M	**Enclosure:** TENV

Nameplate Data			
Rated Output (HP)			.33
Volts			208-230/460
Full Load Amps			1.5-1.7/.85
R.P.M.			1780
Hz	60	**Phase**	3
NEMA Design Code	B	**KVA Code**	S
Service Factor (S.F.)			1.25
NEMA Nom. Eff.	75.5	**Power Factor**	49
Rating - Duty			40C AMB-CONT
S.F. Amps			1.9-1.8/.9

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	0.977 LB-FT
Start Configuration	direct on line
Breakdown Torque	6.28 LB-FT
Pull-up Torque	3.26 LB-FT
Locked-rotor Torque	4.04 LB-FT
Starting Current	6.71 A
No-load Current	0.792 A
Line-line Res. @ 25ºC	43.2 Ω
Temp. Rise @ Rated Load	49°C
Temp. Rise @ S.F. Load	53°C
Locked-rotor Power Factor	70.8
Rotor inertia	0.0866 lb-ft²

Load Characteristics 460 V, 60 Hz, 0.33 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	22	31	41	49	57	63	57
Efficiency	47.4	63.1	70.8	75.1	77.6	79.1	77.6
Speed	1794	1789	1785	1780	1774	1769	1774
Line amperes	0.786	0.791	0.814	0.839	0.878	0.933	0.878


ABB Motors and Mechanical Inc.


WINDING # 35WGG155

0.33 HP 3 PH 60 HZ 1780 RPM 460 V 3512M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=6.28 PU=3.26 LR=4.04 LRA=6.71




35LYS603
510-520 = 11.05
521-528 = 12.06
529-535 = 12.93
536-546 = 14.30
2.06
.13
1.88
4 HOLES
3 W/PLUGS
(EACH END)
.19 KEY
1.38 LONG
NAMEPLATE
Ø 4.500
4.497
Ø6.49
Ø .6250
.6245
V-RING
SLINGER
& SEAL
2.59
Ø6.61
5.65
45°
45°
LEAD HOLE
.50 N.P.T
4 HOLES
.38-16 TAP ON
5.88 DIA. B.C.
4.56
APPLY COAT OF
SEALER UNDER SCREW
HEADS AND TO SEAL
HOUSING BEFORE
PRESSING IN SEAL
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE 3D MODEL BOM PER REV X, NO CHG TO 2D PRINT
REV: H
VERSION: 08
REVISED: 01:11:03 03/10/2022
TDR: 000001187335
MODEL NO: 35LYS603
REF: -
BY: USBUFRA
Material: -
B
BALDOR - RELIANCE®
STD VERT 56C TENV 35M WD (S/P #9)
SH 1 of 1
35LYS603

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS