



Customer information packet

XL050245A

.25HP, 1725RPM, 1PH, 60HZ, 56, 3414L, XPFC, F1

Class - CLI GP C,D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.250 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 115.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UL
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.000 A @ 208.0 V 2.100 A @ 230.0 V 4.200 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	62.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater

Part detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	34WGY855
Layout	34LY6864
Eff. date	06-08-2023
CD Diagram	CD0565
Poles	04
Leads	7#18
Proprietary	False
Created date	04-21-2021

High Voltage Full Load Amps	2.0 a
Insulation Class	B
Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3414L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	13.22 IN
Power Factor	64
Product Family	Hazardous Location Motor
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	EP
Winding Thermal 2	None

Nameplate

NP0301XPSL					
NO.		CC			
SER.					
SPEC.	34-0000-0419				
CAT.NO.	XL050245A				
HP	.25	T. CODE	T3C		
VOLTS	115/208-230				
AMPS	4.2/2-2.1				
RPM	1725 34WGY855				
HZ	60	PH	1	CL	B
SER.F.	1.00	DES	N	CODE	L
RATING	40C AMB-CONT				
FRAME	56	NEMA-NOM-EFF	62		
USABLE AT 208V	N/A	PF	64		
BLANK	NEMA MG-1 PART 5, IP54				

AC Induction Motor Performance Data

Record # 36349

Typical performance - not guaranteed values

Winding: 34WGY855-R006		Type: 3414L		Enclosure: XPFC	
Nameplate Data			230 V, 60 Hz: High Voltage Connection		
Rated Output (HP)	.25	Full Load Torque	0.762 LB-FT		
Volts	115/208-230	Start Configuration	direct on line		
Full Load Amps	4.2/2-2.1	Breakdown Torque	2.38 LB-FT		
R.P.M.	1725	Pull-up Torque	1.68 LB-FT		
Hz	60 Phase	1	Locked-rotor Torque	2.83 LB-FT	
NEMA Design Code	N	KVA Code	L	Starting Current	10.8 A
Service Factor (S.F.)			1	No-load Current	1.67 A
NEMA Nom. Eff.	62	Power Factor	64	Line-line Res. @ 25°C	9.23 Ω A Ph 8.97 Ω B Ph
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	43°C	

Load Characteristics 230 V, 60 Hz, 0.25 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	35	47	54	64	69	72
Efficiency	35.2	50	60.6	61.8	65.7	71.6
Speed	1780	1767	1753	1738	1722	1711
Line amperes	1.69	1.78	1.88	2.07	2.23	2.35


ABB Motors and Mechanical Inc.

WINDING # 34WGY855

0.25 HP 1 PH 60 HZ 1725 RPM 230 V 3414L

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=2.38 PU=1.68 LR=2.83 LRA=10.8



5/29/2024 ACPERF, record # 36349

AC Induction Motor Performance Data

Record # 41431

Typical performance - not guaranteed values

Winding: 34WGY855-R006			Type: 3414L	Enclosure: XPFC	
Nameplate Data			115 V, 60 Hz: Low Voltage Connection		
Rated Output (HP)	.25		Full Load Torque	0.762 LB-FT	
Volts	115/208-230		Start Configuration	direct on line	
Full Load Amps	4.2/2-2.1		Breakdown Torque	2.38 LB-FT	
R.P.M.	1725		Pull-up Torque	1.68 LB-FT	
Hz	60	Phase	1	Locked-rotor Torque	2.83 LB-FT
NEMA Design Code	N	KVA Code	L	Starting Current	21.6 A
Service Factor (S.F.)			1	No-load Current	3.34 A
NEMA Nom. Eff.	62	Power Factor	64	Line-line Res. @ 25°C	2.22 Ω A Ph 8.87 Ω B Ph
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load		

Load Characteristics 115 V, 60 Hz, 0.25 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	35	47	55	64	69	72
Efficiency	35.2	50	60.6	61.9	65.6	71.2
Speed	1780	1767	1753	1738	1722	1711
Line amperes	3.38	3.56	3.76	4.14	4.46	4.7


ABB Motors and Mechanical Inc.

WINDING # 34WGY855

0.25 HP 1 PH 60 HZ 1725 RPM 115 V 3414L




Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=2.38 PU=1.68 LR=2.83 LRA=21.6




5/29/2024 ACPERF, record # 41431

34LY6864



FRONT END DETAIL



PULLEY END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: LOAD TO SOLIDWORKS - REV F

REV: G VERSION: 07 REVISED: 03:04:45 12/16/2022 TDR: 000001201165

34LY6864

MODEL NO. 34LY6864
BY: ENFRAJ0

REF: -


BALDOR - RELIANCE®

HORZ X34L 56 XPFC, CL-I GP-C&D, CL-II GP-F&G, .75 NPT

34LY6864

CD0565

8-RED 1-BLU 2-WHT 3-ORG 4-YEL J-BRN 5-BLK




	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J,8
LOW STD	1,3,8	4	-	2,J,5
LOW OPP	1,3,5	4	-	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CONNECTIONS FOR TWO-TERMINAL THERMAL



REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: C	BY: JLP	REVISED: 04/08/99 3:25	TDR: 0178636
99000		FILE: AAA00014311	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE L, DV, REV, THERMAL, 7 LD, 34XP

CD0565