ABB BALDOR RELIANCE

Customer information packet

XL050522A

0.5HP, 3450RPM, 1PH, 60HZ, 56, 3420L, XPFC, F1
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 9:08:50 PM

Specifications

Enclosure	XPFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.700 A @ 230.0 V
	9.400 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	60.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	4.7 a
Insulation Class	B

Part Detail

Revision	F
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	34WG0656
Layout	34LY5492
Eff. date	05-01-2024
CD Diagram	CD0565
Poles	02
Leads	6#18,1#16 4TH
Proprietary	False
Created date	05-07-2021

Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3420L
Mounting Arrangement	F1
Number of Poles	2
Overall Length	14.22 IN
Power Factor	60
Product Family	Hazardous Location Motor
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	EP
Winding Thermal 2	None

Nameplate

NP0016XPSL							
NO.			**CC**				
SER. #							
SPEC	34-0000-0421						
CAT.NO.	XL050522A						
H.P.	.5		**T. CODE**	T3C			
VOLTS	115/230						
AMPS	9.4/4.7						
R.P.M.	3450 34WG0656						
HZ	60	**PH**	1		**CLASS**	B	
SER.F.	1.00		**DES**	N	**CODE**	N	
RATING	40C AMB-CONT						
FRAME	56				**NEMA NOM. EFF**	60	
		PF	60				
BLANK	NEMA MG-1 PART 5, IP54						

AC Induction Motor Performance Data
Record # 88187
Typical performance - not guaranteed values

Winding: 34WG0656	**Type:** 3420L	**Enclosure:** XPFC

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			0.5	**Full Load Torque**	0.753 LB-FT
Volts			115/230	**Start Configuration**	Unknown
Full Load Amps			9.4/4.7	**Breakdown Torque**	2.82 LB-FT
R.P.M.			3450	**Pull-up Torque**	2.31 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	3.13 LB-FT
NEMA Design Code	N	**KVA Code**	N	**Starting Current**	44.9 A
Service Factor (S.F.)			1	**No-load Current**	8.19 A
NEMA Nom. Eff.	60	**Power Factor**	60	**Line-line Res. @ 25ºC**	0.782 Ω A Ph 2.48 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	69°C
				Locked-rotor Power Factor	95.1
				Rotor inertia	0.0186 lb-ft²

Load Characteristics 115 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	35	44	53	60	67	72
Efficiency	27.8	42.6	51.4	56.9	60.2	62.1
Speed	3561	3540	3516	3491	3464	3434
Line amperes	8.33	8.59	8.97	9.48	10.1	10.9


ABB Motors and Mechanical Inc.

WINDING # 34WG0656

0.5 HP 1 PH 60 HZ 3450 RPM 115 V 3420L


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=2.82 PU=2.31 LR=3.13 LRA=44.9




11/17/2026 ACPERF, record # 88187

34LY5492







PULLEY END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION


REV. DESC: LOAD TO SOLIDWORKS - REV E			
REV: F	VERSION: 04	REVISED: 03:20:37 05/11/2023	TDR: 000001201165
34LY5492	MODEL NO. 34LY5492		REF: -
	BY: ENFRAJ0		

BALDOR - RELIANCE®

HORZ X34L 56 XPFC CL-I GP-D, CL-II GP-F&G

34LY5492

CD0565




	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J.8
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CONNECTIONS FOR TWO–TERMINAL THERMAL



CD0565

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: C	BY: JLP	REVISED: 04/08/99 3:25	TDR: 0178636
CD0565		FILE: AAA00014311	MDL: –
		MTL: –	

BALDOR ELECTRIC Co.

TYPE L, DV, REV, THERMAL, 7 LD, 34XP