Customer information packet

XM050542-5

.5HP, 1770RPM, 3PH, 60HZ, 56, 3512M, XPFC, F1, N
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/14/2026 11:42:40 PM

Specifications

Enclosure	XPFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	.770 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	0.8 a
Insulation Class	F

Part Detail

Revision	D
Type	AC
Mech. spec.	35E354
Base	
Status	PRD/A
Elec. spec.	35WGG200
Layout	35LYE354
Eff. date	07-02-2025
CD Diagram	CD0006
Poles	04
Leads	3#18
Proprietary	False
Created date	02-23-2023

Inverter Code	Not Inverter
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X3512M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.28 IN
Power Factor	62
Product Family	Hazardous Location Motor
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0887XPSLEV

NO.				**CC**					
S/N				**TEMP CODE**	T3C				
SPEC.	35E354G200			**INV.TYPE**	PWM				
CAT.NO.	XM050542-5			**C HP FR**	60	**C HP TO**	90		
HP	.5			**CT HZ FROM**	6			**CT HZ TO**	60
VOLTS	575			**VT HZ FROM**	6			**VT HZ TO**	60
AMPS	.77		**MAG CUR**	.7					
RPM	1770		**MX RPM**	2700					
HZ	60	**PH** 3	**CL** F	**NOM.EFF.**	77				
SER.F.	1.00	**DES** B	**SL HZ**	1	**WK2**	0.087			
FRAME	56	**RATING**	40C AMB-CONT						
	1.15 SF ON SINE WAVE								

AC Induction Motor Performance Data
Record # 39332
Typical performance - not guaranteed values

Winding: 35WGN367-R004	**Type:** 3512M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			.5	**Full Load Torque**	1.49 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			.7	**Breakdown Torque**	6.65 LB-FT
R.P.M.			1740	**Pull-up Torque**	4.62 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	5.25 LB-FT
NEMA Design Code	B	**KVA Code**	M	**Starting Current**	5.05 A
Service Factor (S.F.)			1.15	**No-load Current**	0.487 A
NEMA Nom. Eff.	78.5	**Power Factor**	69	**Line-line Res. @ 25ºC**	53.6 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	27°C
S.F. Amps				**Temp. Rise @ S.F. Load**	31°C
				Locked-rotor Power Factor	74
				Rotor inertia	0.0709 LB-FT2

Load Characteristics 575 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	28	45	58	69	75	80	73
Efficiency	59.5	73.1	78.5	79.8	80.1	78.9	80
Speed	1788	1774	1759	1741	1722	1702	1730
Line amperes	0.5	0.536	0.596	0.676	0.766	0.88	0.73


ABB Motors and Mechanical Inc.

WINDING # 35WGN367


0.5 HP 3 PH 60 HZ 1740 RPM 575 V 3512M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=6.65 PU=4.62 LR=5.25 LRA=5.05





11/14/2026 ACPERF, record # 39332


35LYE354
510-520 = 14.28
521-528 = 15.15
529-535 = 16.03
536 - 546 = 17.40
2.40
1.88
.19 KEY
1.38 LONG
Ø7.19
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
Ø .6250
.6245
4.72
3.00
2.75
.66
4 SLOTS
.34 WIDE
4.32
6.67
6.92
7.07
3.50
3.44
LEAD HOLE
.50 N.P.T.
2.49
2.49
5.33
3.31
6.62
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD TO SOLIDWORKS
REV: F
VERSION: 02
REVISED: 08:32:17 08/30/2019
TDR: 000001117187
MODEL NO. 35LYE354
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ 56 XPFC X35M CL I-GP D-CL II-GP F&G
35LYE354


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1