

ABB BALDOR RELIANCE III

Customer information packet

VXM21722T

7.5//5HP, 3520//2920RPM, 3PH, 60//50HZ, 213T

Class - CLI GP D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	213TC
Frame Material	Steel
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ 5.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 190.0 V @ 50 HZ 230.0 V @ 60 HZ 380.0 V @ 50 HZ
Agency Approvals	UL CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	15.400 A @ 190.0 V 18.000 A @ 230.0 V 7.700 A @ 380.0 V 9.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	37WGR224
Layout	37LY-000-164
Eff. date	04-16-2026
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	03-05-2021

Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	7.7 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3728M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	19.19 IN
Power Factor	84
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP0887XPSLEV

NO.		CC	010A	
S/N		TEMP CODE	T3C	
SPEC.	37-0000-0328	INV.TYPE	PWM	
CAT.NO.	VXM21722T	C HP FR	60	C HP TO 90
HP	7.5//5	CT HZ FROM	6	CT HZ TO 60
VOLTS	230/460//190/380	VT HZ FROM	6	VT HZ TO 60
AMPS	18/9//15.4/7.7	MAG CUR	7.4/3.7	
RPM	3520//2920	MX RPM	5400	
HZ	60//50	PH	3	CL F
		NOM.EFF.	89.5	
SER.F.	1.00	DES	A	SL HZ 1.7
		WK2	0.255	
FRAME	213TC	RATING	40C AMB-CONT	
	NEMA MG-1 PART 5, IP54			
	1.15 SF ON SINE WAVE			


ABB Motors and Mechanical Inc.

WINDING # 37WGR224


7.5 HP 3 PH 60 HZ 3515 RPM 460 V 3728M

Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=39.7 PU=20.6 LR=21.8 LRA=68.4



7/8/2026 ACPERF, record # 73679



CD0005




LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS