

ABB BALDOR RELIANCE III

Customer information packet

VXT3032T-5

3HP, 3500RPM, 3PH, 60HZ, 182TC, 0628M, TEFC, F1

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	182TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR NEMA_PREMIUM NEMA PREMIUM CSA EEV CCSA US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	2.700 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	88.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	06WGW042
Layout	06LYH799
Eff. date	11-27-2024
CD Diagram	CD0006
Poles	02
Leads	3#16
Proprietary	False
Created date	05-18-2021

High Voltage Full Load Amps	2.7 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0628M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	15.98 IN
Power Factor	92
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4224L									
CAT.NO.	VXT3032T-5					I.P.	54		
SPEC.	06-0000-0929					ENCL	TEFC		
FRAME	182TC	H.P.	3			T. CODE	T3C		
VOLTS	575		P.F.	92					
F.L. AMPS	2.7		RATING		40C AMB-CONT				
R.P.M.	3500								
HZ.	60	PH.	3	CLASS		F			
SER.F.	1.00	DES.	B	SL HZ		1.8			
NEMA NOM. EFF.	88.5	WK2		0.13					
DE	6206	ODE		6205					
MAG. CUR.	.8								
INV TYPE	PWM	CHP	60	TO	90	INV TEMP CODE		T3C	
CT	6	TO	60	VT	6	TO	60		
CC	010A	SN							
1.15 SF ON SINE WAVE									

AC Induction Motor Performance Data

Record # 88447

Typical performance - not guaranteed values

Winding: 06WGW042-R001			Type: 0628M		Enclosure: TEFC		
Nameplate Data			575 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		3	Full Load Torque		4.52 LB-FT		
Volts		575	Start Configuration		direct on line		
Full Load Amps		2.7	Breakdown Torque		17.1 LB-FT		
R.P.M.		3500	Pull-up Torque		8.25 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		9.75 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		21.3 A
Service Factor (S.F.)		1.15	No-load Current		0.776 A		
NEMA Nom. Eff.		88.5	Power Factor	92	Line-line Res. @ 25°C		6.43 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		35°C	
S.F. Amps				Temp. Rise @ S.F. Load		41°C	
				Locked-rotor Power Factor		44.3	
				Rotor inertia		0.126 lb-ft²	

Load Characteristics 575 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	72	86	91	93	94	95	94
Efficiency	71.9	81.5	84.6	85.5	85.4	84.8	85.4
Speed	3569	3544	3517	3489	3458	3426	3470
Line amperes	1.09	1.6	2.18	2.82	3.49	4.2	3.22


ABB Motors and Mechanical Inc.


WINDING # 06WGW042

Typical performance - not guaranteed values.




3 HP 3 PH 60 HZ 3500 RPM 575 V 0628M

TORQUES (LB-FT): PO=17.1 PU=8.25 LR=9.75 LRA=21.3





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: —


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1