

ABB BALDOR RELIANCE III

Customer information packet

XEFRPM21104

10HP, 1800, 460V, HL215T, TEFC, F1

Specifications

Enclosure	TEFC
Frame	HL215T
Frame Material	Exposed Laminations
Frequency	60.00 Hz
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSA US NEMA PREMIUM
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Constant Torque Speed Range	1-60
Current @ Voltage	10.000 A @ 460.0 V
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Frame Prefix	HL
Heater Indicator	No Heater
High Voltage Full Load Amps	10.0 a
Insulation Class	H
KVA Code	G
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	21.72 IN
Product Family	Fan - Centrifugal
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible

Part Detail

Revision	J
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	LS7015A
Layout	619704-001
Eff. date	04-23-2019
CD Diagram	422927-001
Poles	04
Leads	
Proprietary	False
Created date	05-20-2016

Speed	1800 rpm
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Nameplate
000613007QF

	DUTY	HP	RPM	AMPS	VOLTS	HZ							
	CONT	10	1800	10.0	460	60							
CAT.NO.	XEFRPM21104		SPEC. NO.		H21-A000-0001								
SER.NO			FRAME SIZE		HL215T		TYPE PSM						
AMB.	40	S.F.	1.15	ENCL.	TEFC	PH	3	DESIGN	B	CODE	G		
NEMA NOM. EFF	94.6	GUARANTEED EFFICIENCY			93.7	POWER FACTOR			98.1	INSUL. CLASS		H	
D.E. BRG.	45BC02J30X		O.D.E. BRG.		35BC02J30X								
VPWM INVERTER DUTY @1.0SF	CHP HZ	60-90		CT HZ	1-60		VT HZ	0-60					
	X/T												

000692000VY


MEAS OPEN CIRCUIT VOLTAGE

IS VOLTS AT RPM.

S.O.	FRAME	HP	TYPE	PHASE	HERTZ	RPM
--	HL215T	10	PSM	3	60	1800
VOLTS	AMPS	DUTY	AMB [°] C	INSUL	S.F.	NEMA DESIGN
460	10.1	CONT	40	H	1.15	B
CODE LETTER	ENCL	ROTOR INERTIA (lb-ft ²)	STATOR RES. @ 25 [°] C OHMS (BETWEEN LINES)			
G	TEFC	.60	1.113	TYPICAL DATA		
PERFORMANCE						
LOAD	HP	AMPERES	RPM	% POWER FACTOR	% EFFICIENCY	
NO LOAD	0	5.6	1800	4.90	N/A	
1/4	2.50	4.4	1800	59.6	89.9	
2/4	4.99	5.6	1800	89.4	93.7	
3/4	7.49	7.7	1800	96.5	94.5	
4/4	9.99	10.1	1800	98.1	94.6	
5/4	12.5	12.6	1800	98.3	94.4	
SPEED TORQUE						
	RPM	TORQUE (% FULL LOAD)	TORQUE (lb-ft)	AMPERES		
LOCKED ROTOR	0	169	49.4	75.0		
PULL OUT	1800	299	87.2	39.5		
FULL LOAD	1800	100	29.1	10.1		
THIS IS A PERMANENT MAGNET MOTOR GENERATED OPEN CIRCUIT LINE-LINE VOLTAGE at 25[°]C = 20.3 VOLTS PER 100 RPM REMARKS:						
		DR. BY <u>CAD</u> CK. BY <u>RFM</u> APP. BY <u>RFM</u> DATE <u>05/25/2016</u>		LSPM MOTOR PERFORMANCE DATA LS7015A ISSUE DATE 05/25/2016		

S.O.	--	HERTZ	60	AMB ^o C	40	CODE LETTER	G
FRAME	HL215T	RPM	1800	INSUL	H	WK ² (lb-ft ²)	.60
HP	10	VOLTS	460	S.F.	1.15	NEMA DESIGN	B
TYPE	PSM	AMPS	10.1	ENCL	TEFC	STATOR RES. @ 25 ^o C	1.113
PHASE	3	DUTY	CONT			OHMS (BETWEEN LINES)	


Amps & Torque vs. RPM During Acceleration



TYPICAL DATA


S.O.	--	HERTZ	60	AMB ^o C	40	CODE LETTER	G
FRAME	HL215T	RPM	1800	INSUL	H	WK ² (lb-ft ²)	.60
HP	10	VOLTS	460	S.F.	1.15	NEMA DESIGN	B
TYPE	PSM	AMPS	10.1	ENCL	TEFC	STATOR RES. @ 25 ^o C	1.113
PHASE	3	DUTY	CONT			OHMS (BETWEEN LINES)	

Performance Data vs. HP At Synchronous Speed



TYPICAL DATA

422927-001



NOTE:
DATA TO BE SIZED
SO THAT IT FITS INTO
MATERIAL DECAL
DIMENSIONS. MAKE
LETTERS & NUMBERS
AS LARGE AS POSSIBLE.

MATERIAL: CERAMATIC DGF-P4
PERMA GRIP ADHESIVE

ALL LETTERS, NUMBERS
AND LINES TO BE BLACK
ON WHITE BACKGROUND.

422927-001

REV. DESC: CHANGE BACKGROUND COLOR FROM GOLD TO WHITE		
REV. LTR: B	VERSION: 02	TDR: 000000788708
FILE: \RGG\00000\203	REVISED: 08:09:29 03/04/2013	
MTL: -	BY: RGGWT	

BALDOR

EXTERNAL CONNECTION LABEL

SH 1 of 1