

ABB BALDOR RELIANCE III

Customer information packet

XM32362T

30//25HP, 1180//980RPM, 3PH, 60//50HZ, 326T

Class - CLI GP D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	326T
Frame Material	Iron
Frequency	50.00 Hz 60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 50 HZ 30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 50 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 380.0 V @ 50 HZ 230.0 V @ 60 HZ 190.0 V @ 50 HZ
Agency Approvals	CSA EEV UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	78.000 A @ 230.0 V 39.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated

Part Detail

Revision	B
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	12WGY812
Layout	12LYL018
Eff. date	11-05-2024
CD Diagram	CD0005
Poles	06
Leads	9#8
Proprietary	False
Created date	03-23-2021

Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	39.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1264M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	32.00 IN
Power Factor	78
Product Family	Hazardous Location Motor
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	2.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0887XPSLEV												
NO.							CC	010A				
S/N							TEMP CODE		T3C			
SPEC.	12-0000-2082						INV.TYPE		PWM			
CAT.NO.	XM32362T						C HP FR		60	C HP TO		90
HP	30//25						CT HZ FROM		6	CT HZ TO		60
VOLTS	230/460//190/380						VT HZ FROM		6	VT HZ TO		60
AMPS	78/39				MAG CUR		34.4/17.2					
RPM	1180//980				MX RPM		1800					
HZ	60//50	PH	3	CL	F	NOM.EFF.		93				
SER.F.	1.00	DES	A	SL HZ		1	WK2	12.2				
FRAME	326T	RATING		40C AMB-CONT								
	NEMA MG-1 PART 5, IP54											
	1.15 SF ON SINE WAVE											

AC Induction Motor Performance Data

Record # 67041

Typical performance - not guaranteed values

Winding: 12WGY812-R015				Type: 1264M		Enclosure: XPFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		30		Full Load Torque		133 LB-FT		
Volts		230/460		Start Configuration		direct on line		
Full Load Amps		78/39		Breakdown Torque		370 LB-FT		
R.P.M.		1180		Pull-up Torque		179 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		217 LB-FT		
NEMA Design Code		A	KVA Code	H		Starting Current		245 A
Service Factor (S.F.)		1		No-load Current		17.2 A		
NEMA Nom. Eff.		93	Power Factor	78		Line-line Res. @ 25°C		0.22799 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		56°C		
				Locked-rotor Power Factor		27.6		

Load Characteristics 460 V, 60 Hz, 30 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	42	63	73	78	80	80
Efficiency	89	92.7	93.4	93.1	92.4	91.4
Speed	1196.5	1191.9	1188.3	1183.2	1178.2	1171.8
Line amperes	19.2	24.1	31	38.7	47.5	57.3


ABB Motors and Mechanical Inc.

WINDING # 12WGY812

Typical performance - not guaranteed values.

30 HP 3 PH 60 HZ 1180 RPM 460 V 1264M

TORQUES (LB-FT): PO=370 PU=179 LR=217 LRA=245



AC Induction Motor Performance Data

Record # 75682

Typical performance - not guaranteed values

Winding: 12WGY812-R018				Type: 1264M		Enclosure: XPFC	
Nameplate Data				380 V, 50 Hz: High Voltage Connection			
Rated Output (HP)		30//25		Full Load Torque		133 LB-FT	
Volts		230/460//190/380		Start Configuration		direct on line	
Full Load Amps		78/39		Breakdown Torque		358 LB-FT	
R.P.M.		1180//980		Pull-up Torque		187 LB-FT	
Hz	60//50	Phase	3	Locked-rotor Torque		227 LB-FT	
NEMA Design Code		A	KVA Code	H	Starting Current		239 A
Service Factor (S.F.)		1		No-load Current		16.97 A	
NEMA Nom. Eff.		93	Power Factor	78	Line-line Res. @ 25°C		0.222 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		56°C	
S.F. Amps				Temp. Rise @ S.F. Load		69°C	
				Locked-rotor Power Factor		30.7	
				Rotor inertia		12.2 LB-FT2	

Load Characteristics 380 V, 50 Hz, 25 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	42	64	74	79	80	81
Efficiency	89.3	92.6	93.1	92.3	91.9	90.6
Speed	996	992	988	984	979	972
Line amperes	18.98	23.98	31.07	38.94	48.02	58.14

ABB Motors and Mechanical Inc.

WINDING # 12WGY812

Typical performance - not guaranteed values.

25 HP 3 PH 50 HZ 984 RPM 380 V 1264M

TORQUES (LB-FT): PO=358 PU=187 LR=227 LRA=239

