

ABB BALDOR RELIANCE III

Customer information packet

XL050762

.75HP, 1165RPM, 1PH, 60HZ, 56, 3540L, XPFC, F1

Class - CLI GP D; CLII GP F,G

Division - Division I

Specifications

Enclosure	XPFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.750 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	UL CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	10.500 A @ 115.0 V 5.250 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	5.3 a

Part Detail

Revision	F
Type	AC
Mech. spec.	35E353
Base	
Status	PRD/A
Elec. spec.	35WGG517
Layout	35LYE353
Eff. date	06-05-2026
CD Diagram	CD0001
Poles	06
Leads	6#18
Proprietary	False
Created date	12-02-2022

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X3540L
Mounting Arrangement	F1
Number of Poles	6
Overall Length	17.40 IN
Power Factor	63
Product Family	Hazardous Location Motor
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1426XPSL					
NO.		CC			
SER.					
SPEC.	35E353G517				
CAT.NO.	XL050762				
HP	.75	T. CODE	T3C		
VOLTS	115/230				
AMPS	10.5/5.25				
RPM	1165				
HZ	60	PH	1	CL	F
SER.F.	1.15	DES	L	CODE	L
RATING	40C AMB-CONT				
FRAME	56	NEMA-NOM-EFF		72	
	PF	63			
BLANK	NEMA MG-1 PART 5, IP54				


ABB Motors and Mechanical Inc.


WINDING # 35WGG517

Typical performance - not guaranteed values.


0.75 HP 1 PH 60 HZ 1165 RPM 115 V 3540L

TORQUES (LB-FT): PO=8.9 PU=4.6 LR=9.5 LRA=47.6





CD0001



CD0001

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:16	TDR: 0178636
100000		FILE: AAA00007405	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE L, DV, REV, 6 LEADS