

BALDOR • RELIANCE

Customer information packet

XT3252TS-5

25HP, 3520RPM, 3PH, 60HZ, 284TS, 1048M, TEFC, F

Class - CLI GP A,B,C,D

Division - Division II

Specifications

Enclosure	TEFC
Frame	284TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP A,B,C,D
Haz Area Division	Division II
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR NEMA_PREMIUM NEMA PREMIUM CSA EEV CCSA US
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	23.000 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3
Heater Indicator	No Heater

Part detail

Revision	A
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	10WGZ277
Layout	10LYR080
Eff. date	07-17-2023
CD Diagram	CD0006
Poles	02
Leads	3#10
Proprietary	False
Created date	07-20-2021

High Voltage Full Load Amps	23.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	F
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1048M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	26.39 IN
Power Factor	90
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4224L									
CAT.NO.	XT3252TS-5				I.P.	54			
SPEC.	10-0000-2237				ENCL	TEFC			
FRAME	284TS	H.P.	25		T. CODE	T3			
VOLTS	575		P.F.	90					
F.L. AMPS	23		RATING	40C AMB-CONT					
R.P.M.	3520		USABLE AT 208V	N/A					
HZ.	60	PH.	3	CLASS	F				
SER.F.	1.00	DES.	B	SL HZ	1.3				
NEMA NOM. EFF.	91.7		WK2	2.07					
DE	6311		ODE	6309					
MAG. CUR.	5.5								
INV TYPE	PWM	CHP	60	TO	90	INV TEMP CODE	T3		
CT	6	TO	60	VT	6	TO	60		
CC	010A	SN							

AC Induction Motor Performance Data

Record # 79887

Typical performance - not guaranteed values

Winding: 10WGZ277-R003		Type: 1048M		Enclosure: TEFC	
Nameplate Data			575 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)		25	Full Load Torque		37.4 LB-FT
Volts		575	Start Configuration		direct on line
Full Load Amps		23	Breakdown Torque		101 LB-FT
R.P.M.		3520	Pull-up Torque		41.3 LB-FT
Hz	60 Phase	3	Locked-rotor Torque		53 LB-FT
NEMA Design Code	B KVA Code	F	Starting Current		134 A
Service Factor (S.F.)		1	No-load Current		5.48 A
NEMA Nom. Eff.	91.7 Power Factor	90	Line-line Res. @ 25°C		0.444 Ω
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		57°C
S.F. Amps			Temp. Rise @ S.F. Load		72°C
			Locked-rotor Power Factor		23.2
			Rotor inertia		2.06 lb-ft ²

Load Characteristics 575 V, 60 Hz, 25 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	69	83	88	90	90	90
Efficiency	87.9	91.5	92.2	91.7	90.9	89.7
Speed	3580	3563	3542	3520	3496	3468
Line amperes	8.03	12.3	17.4	22.7	28.5	34.9


ABB Motors and Mechanical Inc.

WINDING # 10WGZ277


Typical performance - not guaranteed values.

25 HP 3 PH 60 HZ 3520 RPM 575 V 1048M

TORQUES (LB-FT): PO=101 PU=41.3 LR=53 LRA=134



9/12/2024 ACPERF, record # 79887



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CONVERT AUTOCAD DRW TO SWD			
REV: G	VERSION: 06	REVISED: 01:24:48 06/28/2023	TDR: 000001211833
MODEL NO. 10LYR080		REF: -	
BY: ENALEM0		B	

BALDOR - RELIANCE®

HORZ TEFC 284-6TS W/STL FAN COVER & 10FN3001

CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -	© □	

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1