ABB BALDOR RELIANCE

Customer information packet

XM21122T

10//7.5HP, 3510//2915RPM, 3PH, 60//50HZ, 215
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/15/2026 7:16:56 AM

Specifications

Enclosure	XPFC
Frame	215T
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 50 HZ
	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 50 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	190.0 V @ 50 HZ
	230.0 V @ 60 HZ
	380.0 V @ 50 HZ
Agency Approvals	UL
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	10.400 A @ 380.0 V
	11.200 A @ 460.0 V
	20.800 A @ 190.0 V
	22.400 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	37WGS627
Layout	37LYN517
Eff. date	09-12-2023
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	04-29-2021

Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	10.4 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Max Speed	5200 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3750M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	20.06 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	3510 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0887XPSLEV											
NO.				**CC**	010A						
S/N				**TEMP CODE**	T3C						
SPEC.	37-0000-0384			**INV.TYPE**	PWM						
CAT.NO.	XM21122T			**C HP FR**	60	**C HP TO**	90				
HP	10//7.5			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	230/460//190/380			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	22.4/11.2//20.8/10.4			**MAG CUR**	1.71/3.42						
RPM	3510//2915			**MX RPM**	5200						
HZ	60//50	**PH**	3	**CL**	F	**NOM.EFF.**	90.2				
SER.F.	1.15	**DES**	B	**SL HZ**	1.5	**WK2**	0.456				
FRAME	215T	**RATING**	40C AMB-CONT								
	55C AMB @ 1.0 SF										
	1.15 SF SINEWAVE				NEMA MG-1 PT 5,IP54						

AC Induction Motor Performance Data
Record # 87974
Typical performance - not guaranteed values

Winding: 37WGS627-R002	**Type:** 3750M	**Enclosure:** TEFC

Nameplate Data			
Rated Output (HP)			10//7.5
Volts			230/460//190/380
Full Load Amps			22.4/11.2//20.8/10.4
R.P.M.			3510
Hz	60//50	**Phase**	3
NEMA Design Code	B	**KVA Code**	H
Service Factor (S.F.)			1
NEMA Nom. Eff.	90.2	**Power Factor**	90
Rating - Duty			40C AMB-CONT

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	14.93 LB-FT
Start Configuration	direct on line
Breakdown Torque	54 LB-FT
Pull-up Torque	25.7 LB-FT
Locked-rotor Torque	29.9 LB-FT
Starting Current	87.3 A
No-load Current	3.29 A
Line-line Res. @ 25ºC	0.73857 Ω
Temp. Rise @ Rated Load	52°C
Locked-rotor Power Factor	29.7

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	61	81	88	90	91	91
Efficiency	89	92.4	92.8	92.3	91.3	90.1
Speed	3578.8	3557.6	3534.8	3510.8	3483.4	3454.5
Line amperes	4.33	6.25	8.6	11.2	14.1	17.1


ABB Motors and Mechanical Inc.


WINDING # 37WGS627

10 HP 3 PH 60 HZ 3510 RPM 460 V 3750M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=54 PU=25.7 LR=29.9 LRA=87.3




37LYN517
(717-735) = 18.19
(736-744) = 19.32
(745-750) = 20.06
(751-756) = 20.82
5.25
3.82
3.38
.31 KEY
2.38 LONG
LISTING
NAMEPLATE
BALDOR
PT. NO. 35CB3500
X-PROOF NAMEPLATE
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
3.50
8.00
Ø9.65
8.39
2.00
REF
GREASE FITTING
(EA. END)
GREASE PLUG
(EA. END)
10.04
5.25 +.00 -.06
LEAD HOLE
.75 N.P.T.
4.25
4.25
6.80
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD PER BOM REV G
REV: B
VERSION: 02
REVISED: 02:09:01 10/25/2022
TDR: 000001198704
MODEL NO. 37LYN517
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ 213-5T XPFC M CLI GP D, CLII GP F&G, INVERTER
37LYN517

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS