


COOLING: FAN COOLED
ACCESSORIES: BEI HS35



NOTE 1 O.D.E. C-FACE & TACHOMETER MOUNTING
1/2-13 TAP, .88 IN. DEEP, ON A $\varnothing 7.25$ IN. BOLT CIRCLE
FACE RUNOUT AND ECCENTRICITY .004 MAX T.I.R.

NOTE 2 SHAFT HEIGHT WILL NOT BE EXCEEDED.
SHIMS UP TO .05mm IN THICKNESS ARE USUALLY
REQUIRED FOR COUPLED OR GEARED MACHINES.


235 AMP TERMINAL BOX SHOWN
ROTATABLE IN 90° INCREMENTS

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: MODEL AND REDRAW IN SOLIDWORKS			
REV: A	VERSION: 01	REVISED: 03:24:12 01/26/2023	TDR: 000001202962
MODEL NO. 617517-477			REF: -
BY: USWATUR			

BALDOR - RELIANCE®

DIM SHT,TEFC,FL2162CZ,FT MT,PROV FOR TACH,MILL BOX F3,HS35



DIMENSIONS ARE IN INCHES SCALE: 1.00
MOTOR WEIGHT: 290 LBS. (MAY VARY 15%)

61/31/-41/