

ABB BALDOR RELIANCE III

Customer information packet

ZDM3584T-5

1.5HP, 1770RPM, 3PH, 60HZ, 145TC, 0522M, TEBC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEBC
Frame	145TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	BLOWER
Current @ Voltage	1.710 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	ENCODER
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.7 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	L

Part Detail

Revision	C
Type	AC
Mech. spec.	05E535
Base	
Status	PRD/A
Elec. spec.	05WGX559
Layout	05LYE535
Eff. date	09-30-2025
CD Diagram	CD0006
Poles	04
Leads	3#18
Proprietary	False
Created date	02-23-2023

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0522M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.08 IN
Power Factor	76
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4539L											
CAT.NO.	ZDM3584T-5										
SPEC.	05E535X559Z1										
FRAME	145TC				H.P.		1.5 TE				
VOLTS	575										
MAG. CUR.	1.05				F.L. AMPS					1.71	
R.P.M.	1770				R.P.M. MAX				2700		
HZ.	60			PH.		3		CLASS		F	
SER.F.	1.00			DES.		B		SL HZ		1	
NEMA NOM. EFF.	86.5			WK2		0.159					
BLWR V	115		PH		1		HZ		60		AMPS .5
RATING	40C AMB-CONT										
DE	6205		ODE		6203						
CC	010A		SN								
	1000:1 CT/VT										

AC Induction Motor Performance Data

Record # 82042

Typical performance - not guaranteed values

Winding: 05WGX559-R002			Type: 0522M		Enclosure: TEFC			
Nameplate Data			575 V, 60 Hz: Single Voltage Motor					
Rated Output (HP)		1.5	Full Load Torque		4.46 LB-FT			
Volts		575	Start Configuration		direct on line			
Full Load Amps		1.71	Breakdown Torque		16.69 LB-FT			
R.P.M.		1768	Pull-up Torque		9.8 LB-FT			
Hz		60	Phase		3	Locked-rotor Torque	11.36 LB-FT	
NEMA Design Code		B	KVA Code		L	Starting Current	14.18 A	
Service Factor (S.F.)			1	No-load Current		1.05 A		
NEMA Nom. Eff.		86.5	Power Factor		76	Line-line Res. @ 25°C		22 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		34°C		
				Locked-rotor Power Factor		62		
				Rotor inertia		0.159 lb-ft²		

Load Characteristics 575 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	35	54	67	76	81	84
Efficiency	75.8	83.9	86.1	86.4	85.5	84.2
Speed	1791	1784	1776	1768	1758	1748
Line amperes	1.1	1.24	1.45	1.72	2.03	2.38


ABB Motors and Mechanical Inc.

WINDING # 05WGX559

Typical performance - not guaranteed values.




1.5 HP 3 PH 60 HZ 1768 RPM 575 V 0522M

TORQUES (LB-FT): PO=16.69 PU=9.8 LR=11.36 LRA=14.18





CD0006


NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10:24:49 02/19/2019

BY: ENBRIRO

MTL: -


BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1