

ABB BALDOR RELIANCE III

Customer information packet

ZDM3584T

1.5HP, 1770RPM, 3PH, 60HZ, 145TC, 0524M, TEBC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEBC
Frame	145TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	BLOWER
Current @ Voltage	2.300 A @ 460.0 V 4.600 A @ 230.0 V 4.640 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	ENCODER
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.3 a

Part Detail

Revision	E
Type	AC
Mech. spec.	05E535
Base	
Status	PRD/A
Elec. spec.	05WGX510
Layout	05LYE535
Eff. date	09-30-2025
CD Diagram	CD0005
Poles	04
Leads	9#18 Y
Proprietary	False
Created date	07-21-2022

Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	M
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0524M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.02 IN
Power Factor	72
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4539L									
CAT.NO.	ZDM3584T								
SPEC.	05E535X510G2								
FRAME	145TC			H.P.	1.5 TE				
VOLTS	230/460								
MAG. CUR.	3/1.5			F.L. AMPS				4.6/2.3	
R.P.M.	1770			R.P.M. MAX			2700		
HZ.	60		PH.	3	CLASS		H		
SER.F.	1.00		DES.	B	SL HZ			1	
NEMA NOM. EFF.	86.5		WK2	0.174					
BLWR V	115	PH	1	HZ	60	AMPS		.5	
RATING	40C AMB-CONT								
DE	6205	ODE		6203					
CC	010A	SN							
	1000:1 CT/VT								

AC Induction Motor Performance Data

Record # 95409

Typical performance - not guaranteed values

Winding: 05WGX510-R004			Type: 0524M		Enclosure: TEBC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		1.5	Full Load Torque		4.48 LB-FT	
Volts		230/460	Start Configuration		direct on line	
Full Load Amps		4.6/2.3	Breakdown Torque		18.8 LB-FT	
R.P.M.		1770	Pull-up Torque		9.6 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque		12.6 LB-FT	
NEMA Design Code		B KVA Code	Starting Current		19.7 A	
Service Factor (S.F.)		1	No-load Current		1.51 A	
NEMA Nom. Eff.		86.5 Power Factor	Line-line Res. @ 25°C		11.8 Ω	
Rating - Duty		40C AMB-CONT	Temp. Rise @ Rated Load		48°C	
			Locked-rotor Power Factor		58.4	
			Rotor inertia		0.173 lb-ft²	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	31	49	63	72	78	81
Efficiency	75.1	83.5	86	86.5	85.8	84.8
Speed	1792	1785	1777	1769	1760	1750
Line amperes	1.56	1.72	1.97	2.28	2.65	3.06


ABB Motors and Mechanical Inc.


WINDING # 05WGX510

Typical performance - not guaranteed values.




1.5 HP 3 PH 60 HZ 1770 RPM 460 V 0524M

TORQUES (LB-FT): PO=18.8 PU=9.6 LR=12.6 LRA=19.7





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005