ABB BALDOR RELIANCE

Customer information packet

ZDWNM3554T

1.5HP, 1770RPM, 3PH, 60HZ, 145TC, 3530M, TENV
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 7:45:08 PM

Specifications

Enclosure	TENV
Frame	145TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.600 A @ 230.0 V
	2.300 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	ENCODER
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.3 a
Insulation Class	H

Part Detail

Revision	C
Type	AC
Mech. spec.	35RR179
Base	
Status	PRD/A
Elec. spec.	35WGG178
Layout	35LYRR179
Eff. date	06-22-2023
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-10-2022

Inverter Code	Not Inverter
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	4500 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3530M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.90 IN
Power Factor	72
Product Family	Wash Down
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1609L							
CAT NO	ZDWNM3554T						
SPEC.	35RR179G178G1						
FRAME	145TC		**HP**	1.5 TE			
VOLTS	230/460						
MAG CUR	2.6/1.3			**FLA**	4.6/2.3		
RPM	1770		**RPM MAX**	4500			
HZ	60	**PH**	3	**CLASS**	H		
SER.F.	1.00	**DES**	B	**SL HZ**	1		
NEMA-NOM-EFF	86.5	**WK2**	0.217				
BLWR V		**PH**		**HZ**		**A**	
RATING	40C AMB-CONT						
DE BRG	6205		**ODE BRG**	6203			
CC	010A	**SER.NO**					

AC Induction Motor Performance Data
Record # 87056
Typical performance - not guaranteed values

Winding: 35WGG178-R003	**Type:** 3530M	**Enclosure:** TENV

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1.5	**Full Load Torque**	4.48 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			4.6/2.3	**Breakdown Torque**	21.02 LB-FT
R.P.M.			1770	**Pull-up Torque**	12.29 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	14.9 LB-FT
NEMA Design Code	B	**KVA Code**	M	**Starting Current**	21.32 A
Service Factor (S.F.)			1	**No-load Current**	1.29 A
NEMA Nom. Eff.	86.5	**Power Factor**	72	**Line-line Res. @ 25ºC**	10.1 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	80°C
				Locked-rotor Power Factor	55.5
				Rotor inertia	0.217 lb-ft²

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	33	54	68	76	81	84
Efficiency	79.1	86.3	88.1	88.3	87.6	86.6
Speed	1790	1783	1776	1769	1761	1752
Line amperes	1.35	1.52	1.78	2.11	2.47	2.89

ABB Motors and Mechanical Inc.

WINDING # 35WGG178

1.5 HP 3 PH 60 HZ 1770 RPM 460 V 3530M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=21.02 PU=12.29 LR=14.9 LRA=21.32




35LYRR179
510-528 = 14.90
529-535 = 15.48
536-546 = 16.86
2.12
2.78
2.59
(4) .125" NPT HOLES
3 W/PLUGS
@ 3,9 & 1:00
(FRONT END)
.13
.13
.19 KEY
1.38 LONG
NAMEPLATE
Ø6.49
Ø 4.500
4.497
Ø .8750
.8745
FORSHEDA
SLINGER
6 HOLES
.34 DIA
4.00
2.75
5.00
.50
5.94
(4) .125" NPT HOLES
3 W/PLUGS
@ 3,9 & 11:00
(PULLEY END)
Ø6.61
5.81
45°
45°
7.05
3.50
3.44
4 HOLES
.38-16 TAP ON
Ø5.88 B.C.
LEAD HOLE
.75 NPT
2.75
2.75
4.62
3.25
6.50
APPLY COAT OF
SEALER TO HOUSING
BEFORE PRESSING
SEAL IN
FRONT END DETAIL
COAT ENTIRE SCREW
HEAD WITH SEALER
BEFORE INSTALLING
.06
APPLY COAT OF
SEALER TO HOUSING
BEFORE PRESSING
SEAL IN
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CHG OFFSET OF FR.BRG, CHG CONFIG OF PU.BRG RET SCR
REV: C
VERSION: 03
REVISED: 11:24:00 01/09/2025
TDR: 000001247833
MODEL NO. 35LYRR179
REF: -
BY: USODDIL
B
BALDOR - RELIANCE®
HOR 143-5TC TENV 35M WD VECTOR (THRU-SHAFT ENCODER)
SH 1 of 1
35LYRR179

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS