



Customer information packet

ZDM3665T-5

5HP, 1750RPM, 3PH, 60HZ, 184TC, 0640M, TEBC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEBC
Frame	184TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	115V 1-Phase EXT
Current @ Voltage	5.200 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	ENCODER
Front Face Code	Encoder/Feedback Device
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	5.2 a
Insulation Class	H
Inverter Code	Inverter Duty

Part detail

Revision	AC
Type	AC
Mech. spec.	06F552
Base	
Status	PRD/A
Elec. spec.	06WGW357
Layout	06LYF552
Eff. date	09-30-2025
CD Diagram	CD0006
Poles	04
Leads	3#16
Proprietary	False
Created date	01-01-0001

KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	6000 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0640M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	21.71 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4539L									
CAT.NO.	ZDM3665T-5								
SPEC.	06F552W357Z1								
FRAME	184TC	H.P.	5 TE						
VOLTS	575								
MAG. CUR.	2.7	F.L. AMPS	5.2						
R.P.M.	1750	R.P.M. MAX	6000						
HZ.	60	PH.	3	CLASS	H				
SER.F.	1.00	DES.	B	SL HZ	1.7				
NEMA NOM. EFF.	90.2	WK2	0.37						
BLWR V	115	PH	1	HZ	60	AMPS	.26		
RATING	40C AMB-CONT								
DE	6206	ODE	6205						
CC	010A	SN							
	1000:1 CT/VT								

**AC Induction Motor Performance Data**

Record # 20660

Typical performance - not guaranteed values

Winding: 06WGW357	Type: 0640M	Enclosure: TEBC
--------------------------	--------------------	------------------------

Nameplate Data			General Characteristics at 575 V, 60 Hz: Single Volt Motor		
Rated Output (HP)	5		Full Load Torque	15 LB-FT	
Volts	575		Start Configuration	DOL	
Full Load Amps	5.2		Break Down Torque	50 LB-FT	
R.P.M.	1750		Pull-Up Torque	30 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque	32 LB-FT
NEMA Design Code	B	KVA Code	J	Starting Current	38 Amps
Service Factor	1.00		No-load Current	2.7 Amps	
NEMA Nom. Eff.	90.2	P.F.	80	Line-line Res. @ 25°C.	3.86 Ohms
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	47°C	
S.F. Amps			Temp. Rise @ S.F. Load		


Load Characteristics at 575 Volts, 60 Hz, 5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	39	61	75	82	86	88	
Efficiency	84.1	89.4	90.4	90.2	89.4	88.3	
Speed	1789	1778	1767	1755	1742	1729	
Line Amperes	2.9	3.4	4.2	5.1	5.8	7.2	


Baldor Electric Company Fort Smith, Arkansas

BALDOR • RELIANCE

Catalog	ZDM3665T-5	NP VOLTS	575	ENCLOSURE	TEBC	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 200)
FRAME	184TC	NP AMPS	5.2	Base Volts	575	R1 1.890 X1 4.353
HP	5 HP	DUTY	Cont	Base AMPS	5.1	R2 1.530 X2 3.402
BASE SPEED	1800	MAX SAFE RPM	6000	Slip Hz	1.50	XM 122.943
PHASE/HZ	3/60	AMB ⁶ /C/INSUL	40/H	Wk ² (lb-ft ²)	0.372	




Remarks: Calculated Data





BALDOR
A MEMBER OF THE ABB GROUP

DR BY	ENR	A-C MOTOR	06F552W357Z1
CK BY	ENR	PERFORMANCE CURVES	
APP BY	ENR		
DATE	2/26/2013	ISSUE DATE	2/26/2013



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIRO
MTL: -	© □	

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1