

BALDOR • RELIANCE

Customer information packet

ZDM3768T

48M 6P TEBC HOR 215TC T'STATS VECTOR

Class - None

Division - Not Applicable

Specifications

Enclosure	TEBC
Frame	215TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	BLOWER
Current @ Voltage	14.600 A @ 230.0 V 7.300 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	ENCODER
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	7.3 a
Insulation Class	H

Part detail

Revision	E
Type	AC
Mech. spec.	07D515
Base	
Status	PRD/A
Elec. spec.	07WGX823
Layout	07LYD515
Eff. date	09-30-2025
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	03-12-2019

Inverter Code	Inverter Duty
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2000 rpm
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0748M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	25.58 IN
Power Factor	72
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible: Connected Standard
Shaft Slinger Indicator	No Slinger
Speed	1160 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4539L			
CAT.NO.	ZDM3768T		
SPEC.	07D515X823Z1		
FRAME	215TC	H.P.	5 TE
VOLTS	230/460		
MAG. CUR.	7.4/3.7	F.L. AMPS	14.6/7.3
R.P.M.	1160	R.P.M. MAX	2000
HZ.	60	PH.	3 CLASS H
SER.F.	1.00	DES.	A SL HZ 2
NEMA NOM. EFF.	90.2	WK2	1.19
BLWR V	PH	HZ	AMPS
RATING	40C AMB-CONT		
DE	6307	ODE	6206
CC	010A SN		
	1000:1 CT/VT		

NP VOLTS	230/460	Base Volt	460	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)		
NP AMPS	14.6/7.3	NL AMPS	3.70	R1	0.000	X1 0.000
HP	5	Slip (HZ)	1.85	R2	0.000	X2 0.000
BASE SPEED	1163	WK ² (lb-ft ²)	1.190			XM 0.000
PHASE/HZ	3/60					

Rated Full Load Data


	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1163	5.1	22.8	460	60	7.3
Max Speed	1741	5.0	15.2	460	90	6.8
CT Min Speed	1,163	0.005	22.8	0.46	0.06	7.3

Load Performance at Base Speed


	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1199	0.0	0.0	460	60	3.7
1/4	1190	1.3	5.6	460	60	4.0
1/2	1181	2.5	11.0	460	60	4.8
3/4	1173	3.7	16.7	460	60	5.9
Full Load	1163	5.1	22.8	460	60	7.3
O/L	1095	10.1	48.4	460	60	16.1

Blower Data	Volts	Ph/Hz	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data

	DR BY	USBRRANI	A-C MOTOR	07WGX823
	CK BY	CD	PERFORMANCE	
	APP BY	USBRRANI	CURVES	
	DATE	11/5/2024		Record: 36499

NP VOLTS	230/460	Base Volt	460	WYE CONN EQ. CRT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	14.6/7.3	NL AMPS	3.70	R1	0.000	X1	0.000
HP	5	Slip (Hz)	1.85	R2	0.000	X2	0.000
BASE SPEED	1163	WK ² (lb-ft ²)	1.190	XM	0.000		
PHASE/HZ	3/60						



Calculated Data
Data Valid For Nameplate Speed Range only

BALDOR • RELIANCE

A-C MOTOR PERFORMANCE CURVES


07WGX823

DR BY USBRRANI
 CK BY CD
 APP BY USBRRANI
 DATE 11/5/2024

Record: 36499

NP VOLTS	230/460	0	0	WYE CONN EQ. CRT OHMS PER PHASE (BASE RATING, 20C)			
NP AMPS	14.6/7.3	Base Volt	460	R1	0.000	X1	0.000
HP	5	NL AMPS	3.70	R2	0.000	X2	0.000
BASE SPEED	1163	Slip (HZ)	1.85	XM	0.000		
PHASE/HZ	3/60	WK2 (lb-ft ²)	1.190				

Vector PWM Inverter Duty
Variable Speed AC Motor Curves




Calculated Data

Data Valid For Nameplate Speed Range only




DR BY	USBRANI	A-C MOTOR	07WGXR23
CK BY	CD	PERFORMANCE	
APP BY	USBRANI	CURVES	
DATE	11/5/2024		Record: 36499



CD0005



LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS