

ABB BALDOR RELIANCE III

Customer information packet

ZDPM18025C-BV

25HP, 1800RPM, 3PH, 60HZ, 1852C, TEBC, FOOT,

Specifications

Enclosure	TEAO
Frame	FL1852C
Frame Material	Aluminum
Frequency	60.00 Hz
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Auxiliary Box	NO AUXILLARY BOX
Base Indicator	Rigid
Bearing Grease Type	No Grease
Current @ Voltage	26.600 A @ 460.0 V
Duty Rating	CONT
Feedback Device	TACHOMETER
Frame Prefix	FL
Heater Indicator	No Heater
High Voltage Full Load Amps	26.6 a
Insulation Class	H
Motor Standards	NEMA
Mounting Arrangement	F3
Overall Length	27.96 IN
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1800 rpm
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat

Part Detail

Revision	E
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	PM3926A
Layout	617235-315
Eff. date	12-21-2021
CD Diagram	422927-001
Poles	04
Leads	
Proprietary	False
Created date	04-09-2015



Nameplate

000692000VY		
MEAS OPEN CIRCUIT VOLTAGE		
IS		VOLTS AT RPM.

000613006MY


	DUTY	HP	RPM	AMPS	VOLTS	HZ	
	CONT	25	1800		26.6	460	60
	CONT	25	3000		25.4	460	100
CAT.NO.	ZDPM18025C-BV		SPEC. NO.		P18M0504		
SER.NO			FR	FL 1852C	INSUL	H	
PH.	3	MAX SAFE SPEED		7200	AMB.	40	MIN. AMB.
DESIGN NO.	PM3926A		TYPE		ENCL.	TEAO-BC	
S.F.	1.0		D.E. BRG.	45BC02JPP30A			
ENCL MOD			O.D.E. BRG.	35BC02JPP30A			

S.O. 0	VOLTS 460	TYPE IPM	STATOR RES. @ 25 °C .3729
FRAME FL1852	AMPS 25.9	ENCLOSURE TEBC	OHMS (BETWEEN LINES)
HP 25	DUTY CONT	MAX SAFE RPM 7200	
BASE SPEED 1800	S.F. 1.0	WK ² (Lb-Ft ²) .96	
PHASE/HERTZ 3/60	AMB °C/INSUL 40/H	MAX INSTANTANEOUS OVERLOAD AMPS 77.7	

VARIABLE SPEED PERFORMANCE

HP	AMPS (rms)	RPM	GAMMA*	POWER FACT.	EFF.	VOLTS (L-L) (rms)	Em (L-N) (rms)	Lq (mH)	Ld (mH)
OpenCkt**	N/A	1800	5.0	N/A	N/A	N/A	191	N/A	N/A
OpenCkt, hot	N/A	1800	5.0	N/A	N/A	N/A	172	N/A	N/A
5.10	6.5	1800	29.0	98.0	92.3	372	172	65.0	7.90
11.4	12.9	1800	37.8	97.2	94.0	416	172	48.0	8.10
18.0	19.4	1800	42.1	96.3	94.9	437	172	39.0	8.20
25.0	25.9	1800	46.5	95.4	95.1	459	172	35.0	8.40

Remarks: TYPICAL DATA
 CONSTANT TORQUE 0-1800 RPM, CONSTANT POWER 1800-3000 RPM
 200% OVERLOAD BELOW BASE SPEED TAPERED TO 100% AT 3000 RPM



*Gamma is the current angle relative to counter emf, defined to be positive when current leads counter emf.

Equivalently, Gamma is positive when Id is negative.

**Data at 25°C - all other data at rated temperature

BALDOR


DR. BY	CD
CK. BY	RM
APP. BY	RM
DATE	4/23/10

IPM MOTOR	
PERFORMANCE DATA	PM3926A
ISSUE DATE	4/23/10

S.O. 0	VOLTS 460	TYPE IPM	STATOR RES. @ 25 °C .3729
FRAME FL1852	AMPS 25.9	ENCLOSURE TEBC	OHMS (BETWEEN LINES)
HP 25	DUTY CONT	MAX SAFE RPM 7200	
BASE SPEED 1800	S.F. 1.0	WK ² (Lb-Ft ²) .96	
PHASE/HERTZ 3/60	AMB °C/INSUL 40/H	MAX INSTANTANEOUS OVERLOAD AMPS 77.7	

Lq, Ld, & Torque vs. RMS Phase Amps

CONSTANT TORQUE 0-1800 RPM, CONSTANT POWER 1800-3000 RPM
200% OVERLOAD BELOW BASE SPEED TAPERED TO 100% AT 3000 RPM



REMARKS: TYPICAL DATA


BALDOR

DR. BY	CD
CK. BY	RM
APP. BY	RM
DATE	4/23/10

**IPM MOTOR
PERFORMANCE
DATA**


PM3926A

ISSUE DATE 4/23/10



INDUSTRIAL ALTERNATING CURRENT MOTORS
RPM AC

STEEL, CAST IRON, MILL AND TERMINAL BOARD CONDUIT BOX DIMENSIONS
NEMA FRAMES RL210 thru RL280 and IEC FRAMES RDL132 thru RDL180
NEMA FRAMES FL180 thru FL280 and IEC FRAMES FDL112 thru FDL180



FRAME	TYPE	TERMINAL STRIP	AMPS	C/BOX	Y	TA	T	AA
FL180	STEEL	N	40	706320003A	5.00	1.62	3.00	1.12
FL180	STEEL	Y/N	75	706320003A	6.12	2.36	4.38	1.75/2.00
FL180	STEEL	N	208	706320007A	6.62	2.00	7.00	2.50/2.00
FL180	CAST IRON	Y/N	208	706320004C	6.75	2.50	4.38	1.0/1.75
FL180 & FDL11	MILL	Y	100	706310056A	7.75	2.30	4.40	PG29/PG16

FL210 & RL210	STEEL	N	61	075452000B	6.34	2.00	4.12	1.75
FL210 & RL210	STEEL	N	121	075452001A	7.69	2.38	5.25	1.94
FL210 & RL210	STEEL	N	306	706320016A	9.00	4.12	8.44	4.59
FL210 & RL210	CAST IRON	N	110	075460052B	7.25	2.50	5.25	1.5 TAP
FL210 & RL210	MILL	Y	100	706310229A	7.75	2.30	4.40	PG29/PG16
FL210 & RL210	MILL	Y	160	706310056A	9.00	3.06	5.40	PG36/PG16
FL210 & RL210	MILL	Y/N	235	706310056B	11.42	4.00	6.72	2.50

FL250 & RL250	STEEL	N	61	075452000B	6.34	2.00	4.12	1.75
FL250 & RL250	STEEL	N	121	075452001A	7.69	2.38	5.25	1.94
FL250 & RL250	STEEL	N	306	706320016A	9.00	4.12	8.44	4.59
FL250 & RL250	CAST IRON	N	110	075460052B	7.25	2.50	5.25	1.5 TAP
FL250 & RL250	CAST IRON	N	210	706320013A	10.50	4.88	9.00	4.0 TAP
FL250 & RL250	MILL	Y	100	706310229A	7.75	2.30	4.40	PG29/PG16
FL250 & RL250	MILL	Y	160	706310056B	9.00	3.06	5.40	PG36/PG16
FL250 & RL250	MILL	Y/N	235	706310057A	11.42	4.00	6.72	2.50
FL250 & RL250	MILL	Y	235	706310063B	14.39	7.43	12.15	BLANK

FL280 & RL280	STEEL	N	160	706320029A	7.25	3.50	7.06	2.50
FL280 & RL280	STEEL	N	306	706320016A	9.00	4.12	8.44	4.59
FL280 & RL280	STEEL	N	500	702658001C	14.62	7.56	12.70	5.00
FL280 & RL280	CAST IRON	N	140	706320012B	9.25	4.81	8.56	3.0 TAP
FL280 & RL280	CAST IRON	N	210	706320013A	10.50	4.88	9.00	4.0 TAP
FL280 & RL280	CAST IRON	N	510	706320014D	15.00	7.56	12.81	5.0 TAP
FL280 & RL280	MILL	Y	100	706310056A	7.75	2.30	4.40	PG29/PG16
FL280 & RL280	MILL	Y	160	706310056B	9.00	3.06	5.40	PG36/PG16
FL280 & RL280	MILL	Y/N	235	706310057A	11.42	4.00	6.72	2.50
FL280 & RL280	MILL	Y	400	706310063B	14.39	7.43	12.15	BLANK

FRAME SIZE	YAB	XA	XY	PART NUMBER	FRAME SIZE	YAB	XA	XY	PART NUMBER
FL210/RL210/FL112	7.38	4.25	4.25	602007-26-A	FL210/RL210/FL112	10.88	8.00	8.00	706310-3-B
FL250/RL250/FL160	8.44	4.25	4.25	602007-26-A	FL250/RL250/FL160	11.88	8.00	8.00	706310-3-B
FL280/RL280/FL280/180	9.12	4.25	4.25	602007-26-A	FL280/RL280/FL280/180	12.62	8.00	8.00	706310-3-B

- (1) 1"AW CONDUIT.
- (2) 1"AW PIPE TAP.
- (3) CUSTOMER TO PROVIDE HOLE PER CONDUIT.
- (4) E ON 5A OR 1 TAP ON 4C.

TERMINAL BOX CAN BE ROTATED FOR LEAD OUTLET AT TOP, SIDES OR BOTTOM.
TERMINAL BOX LOCATED ON OPPOSITE SIDE WHEN F-2, V-1, V-4, V-5, V-7,
OR C-1 MOUNTING IS SPECIFIED. BOX LOCATED ON TOP WHEN SPECIFIED.


CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.

REV. DESC: ADD 706310-637 & 639 BOX	TDR: 000001180260
REV. LTR: F	VERSION: 06
FILE: \\RGG\00003\692	REVISED: 11:08:56 10/26/2021
MTL: -	BY: RCGRWM

BALDOR - RELIANCE®

DIM SHT NEMA RL210-RL280 FL180-FL280 IEC RDL132-RDL180

422927-001



NOTE:
DATA TO BE SIZED
SO THAT IT FITS INTO
MATERIAL DECAL
DIMENSIONS. MAKE
LETTERS & NUMBERS
AS LARGE AS POSSIBLE.

MATERIAL: CERAMATIC DGF-P4
PERMA GRIP ADHESIVE

ALL LETTERS, NUMBERS
AND LINES TO BE BLACK
ON WHITE BACKGROUND.

422927-001

REV. DESC: CHANGE BACKGROUND COLOR FROM GOLD TO WHITE		
REV. LTR: B	VERSION: 02	TDR: 000000788708
FILE: \RGG\00000\203	REVISED: 08:09:29 03/04/2013	
MTL: -	BY: RGGWT	

BALDOR

EXTERNAL CONNECTION LABEL

SH 1 of 1