ABB BALDOR RELIANCE

Customer information packet

ZDVSNM2237T

7.5HP, 1760RPM, 3PH, 60HZ, 215TC, 0748M, TENV
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/17/2026 8:38:18 PM

Specifications

Enclosure	TENV
Frame	215TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	17.800 A @ 230.0 V
	8.900 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	92.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	ENCODER
Front Face Code	Encoder/Feedback Device
Front Shaft Indicator	No Key Or Flat
Heater Indicator	No Heater
High Voltage Full Load Amps	8.9 a

Part Detail

Revision	H
Type	AC
Mech. spec.	07M293
Base	
Status	PRD/A
Elec. spec.	07WGX647
Layout	07LYM293
Eff. date	09-30-2025
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	11-14-2014

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	6000 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0748M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	20.86 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP4357L							
CAT NO	ZDVSNM2237T						
SPEC.	07M293X647G1						
FRAME	215TC		**HP**	7.5 TE			
VOLTS	230/460						
MAG CUR	7.2/3.6			**FLA**	17.8/8.9		
RPM	1760		**RPM MAX**	6000			
HZ	60	**PH**	3	**CLASS**	F		
SER.F.	1.00		**SL HZ**	1.33			
NEMA-NOM-EFF	92.4	**WK2**	1.18				
RATING	40C AMB-CONT						
DE BRG	6307	**ODE BRG**	6206				
CC	010A	**SN**					
	1.5:1 CHP PWM						
	1000:1 CT/VT						

Catalog	ZDVSNM2237T	NP VOLTS	230/460	ENCLOSURE	TENV	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
FRAME	215TC	NP AMPS	17.8/8.9	MAX SAFE RPM	2700	R1	0.712	X1	2.675
HP	7.5	DUTY	Cont	NL AMPS	3.53	R2	0.463	X2	2.17
BASE SPEED	1760	S.F.	1.00	P.F. @NL/FL	0/82			XM	70.294
PHASE/HZ	3/60	AMB^{0}C/INSUL	40/F	WK^2 (lb-ft^2)	1.18				

Rated Full Load Data

	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1762	7.5	22.4	460	60	9.1
Max Speed	2641	7.5	14.9	460	90	8.8
Min Speed	0	0.0	22.4	26.81	1.27	9.1

Load Performance at Base Speed

	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1799	0.0	0.0	460	60	3.5
1/4	1790	1.8	5.4	460	60	4.1
1/2	1781	3.8	11.1	460	60	5.4
3/4	1771	5.6	16.7	460	60	7.1
Full Load	1762	7.5	22.4	460	60	9.1
O/L	1727	15.0	45.6	460	60	18.3

Blower Data	Volts	Ph/Hz	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data
Vector PWM Inverter Duty

Catalog	ZDVSNM2237T	VOLTS	230/460	ENCLOSURE	TENV	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
FRAME	215TC	AMPS	17.8/8.9	MAX SAFE RPM	2700	R1	0.712	X1	2.675
HP	7.5	DUTY	Cont	In (AMPS)	3.53	R2	0.463	X2	2.174
BASE SPEED	1760	S.F.	1.00	P.F. @NL/FL	0/82			XM	70.294
PHASE/HZ	3/60	AMB^{0}C/INS	40/F	WK^2 (lb-ft^2)	1.18				

Vector PWM Inverer Duty

Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only

Catalog	ZDVSNM2237T	NP VOLTS	230/460	ENCLOSURE	TENV	WYE CONN EQ CKT OHMS PER PHASE (BASE RATING, 20C)			
FRAME	215TC	NP AMPS	17.8/8.9	MAX SAFE RPM	2700	R1	0.712	X1	2.675
HP	7.5	DUTY	Cont	NL AMPS	3.53	R2	0.463	X2	2.174
BASE SPEED	1760	S.F.	1.00	P.F. @NL/FL	0/82			XM	70.294
PHASE/HZ	3/60	AMB^{0}C/INSUL	40/F	WK^2 (lb-ft^2)	1.18				

Vector PWM Inverer Duty

Vaiable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only

BALDOR
A MEMBER OF THE ABB GROUP

DR BY	HDO
CK BY	
APP BY	HDO
DATE	3/17/2015

A-C MOTOR PERFORMANCE CURVES

07M293X647G1

ISSUE DATE 3/17/2015


07LYM293
(717-750) = 20.86
9.73
GREASE FITTING (EA END)
.26
3.12
.31 KEY 2.38 LONG
9.06
8.500
8.497
Ø 1.3750
1.3745
8 HOLES .41 DIA.
5.50
4.24
5.50
.56
8.13
11.50
9.37
6.00
2.04
4 HOLES .50-13 TAP ON 7.25 DIA. B.C.
10.99
5.25 +.00 -.06
LEAD HOLE 1.38 DIA.
4.25
4.25
7.37
4.92
9.83
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: B
VERSION: 02
REVISED: 01:08:23 12/22/2022
TDR: 000001201569
MODEL NO. 07LYM293
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 213-5TC TENV V*S MASTER VECTOR W/ BEI HS35
07LYM293

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS