ABB BALDOR RELIANCE

Customer information packet

ZDVSNM3661T

3HP, 1760RPM, 3PH, 60HZ, 182TC, 0636M, TENV, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/8/2026 5:26:30 AM

Specifications

Enclosure	TENV
Frame	182TC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	UR
	CSA
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.300 A @ 460.0 V
	8.600 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	ENCODER
Front Face Code	Encoder/Feedback Device
Front Shaft Indicator	No Key Or Flat
Heater Indicator	No Heater
High Voltage Full Load Amps	4.3 a

Part Detail

Revision	L
Type	AC
Mech. spec.	06H929
Base	
Status	PRD/A
Elec. spec.	06WGX370
Layout	06LYH929
Eff. date	09-30-2025
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	09-05-2012

Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	6000 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0636M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	17.85 IN
Power Factor	73
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP4357L					
CAT NO	ZDVSNM3661T				
SPEC.	06H929X370Z1				
FRAME	182TC	**HP**	3 TE		
VOLTS	230/460				
MAG CUR	4.8/2.4		**FLA**	8.6/4.3	
RPM	1760	**RPM MAX**	6000		
HZ	60	**PH**	3	**CLASS**	F
SER.F.	1.00	**SL HZ**	1.2		
NEMA-NOM-EFF	89.5	**WK2**	0.372		
RATING	40C AMB-CONT				
DE BRG	6206	**ODE BRG**	6206		
CC	010A	**SN**			
	1.5:1 CHP PWM				
	1000:1 CT/VT				

REL S.O.	ZDVSNM3661T	VOLTS	460	ENCLOSURE	TENV	WYE CONN EQ CKT OHMS PER PHASE			
FRAME	182TC	AMPS	4.1	MAX SAFE RPM	6000	(AT BASE RATING, 25^{0}C)			
HP	3	DUTY	CONT	In (AMPS)	2.4	R1	1.8960	X1	5.0400
BASE SPEED	1760	S.F.	1.0	P.F. @NL/FL	6/73	R2	1.3540	X2	4.2900
PHASE/HZ	3/60	AMB^{0}C/INSUL	40/F	WK^2 (lb-ft^2)	0.326			XM	112.2000

Rated Full Load Data

	RPM	HP	Torque	Volts	Freq-Hz	Amps
Base Speed	1765	3.0	8.98	460	60	4.29
Max Speed	2630	3.0	6.04	460	90	3.90
Min Speed	0	0.0	9.00	31.64	1.17	4.29

Load Performance at Base Speed

	RPM	HP	Torque	Volts	Freq-Hz	Amps
No Load	1799	0.0	0.00	460	60	2.40
1/4	1791	0.8	2.30	460	60	2.67
1/2	1783	1.5	4.51	460	60	3.04
3/4	1774	2.3	6.71	460	60	3.61
Full Load	1765	3.0	8.98	460	60	4.29
O/L	1735	5.0	15.20	460	60	6.60


Blower Data	Volts	Ph/Hz	FL Amps	LR Amps	Frame	CFM

Remarks: Calculated Data
Vector PWM Inverter Duty

BALDOR A MEMBER OF THE ABB GROUP	DR BY Micheal Williamson CK BY Micheal Williamson APP BY Micheal Williamson DATE 5/14/2013	A-C MOTOR PERFORMANCE CURVES	**06H929X370Z1** ISSUE DATE 5/14/2013

REL S.O.	ZDVSNM3661T	VOLTS	460	ENCLOSURE	TENV	WYE CONN EQ CKT OHMS PER PHASE			
FRAME	182TC	AMPS	4.1	MAX SAFE RPM	6000	(AT BASE RATING, 25^{0}C)			
HP	3	DUTY	CONT	In (AMPS)	2.4	R1	1.8960	X1	5.0400
BASE SPEED	1760	S.F.	1.00	P.F. @NL/FL	6/73	R2	1.3540	X2	4.2900
PHASE/HZ	3/60	AMB^{0}C/INSUL	40/F	WK^2 (lb-ft^2)	0.326			XM	112.2000

Vector PWM Inverer Duty
Variable Speed AC Motor Curves




Calculated Data

Data Valid For Nameplate Speed Range only

BALDOR A MEMBER OF THE ABB GROUP	DR BY Micheal Williamson CK BY Micheal Williamson APP BY Micheal Williamson DATE 5/14/2013	A-C MOTOR PERFORMANCE CURVES	06H929X370Z1 SH 1 of 2 ISSUE DATE 5/14/2013

REL S.O.	ZDVSNM3661T	VOLTS	460	ENCLOSURE	TENV	WYE CONN EQ CKT OHMS PER PHASE			
FRAME	182TC	AMPS	4.1	MAX SAFE RPM	6000	(AT BASE RATING, 25^{0}C)			
HP	3	DUTY	CONT	In (AMPS)	2.4	R1	1.8960	X1	5.0400
BASE SPEED	1760	S.F.	1.00	P.F. @NL/FL	6/73	R2	1.3540	X2	4.2900
PHASE/HZ	3/60	AMB^{0}C/INSUL	40/F	WK^2 (Lb-Ft^2)	0.326			XM	112.2000

Vector PWM Inverer Duty
Variable Speed AC Motor Curves



Calculated Data

Data Valid For Nameplate Speed Range only


BALDOR
A MEMBER OF THE ABB GROUP

DR BY Micheal Williamson
CK BY Micheal Williamson
APP BY Micheal Williamson
DATE 5/14/2013


A-C MOTOR
PERFORMANCE CURVES


06H929X370Z1

SH 2 of 2
ISSUE DATE 5/14/2013


06LYH929
(614-643) = 17.85
8.85
2.75
.25
2.62
.25 KEY
1.75 LONG
AUX NAMEPLATE
(WHEN REQ'D)
GREASE FITTING
(EA. END)
BALDOR
8.86
Ø 8.500
8.497
Ø 1.1250
1.1245
PROTECTIVE COVER
(MOUNT WITH
CONNECTOR OPENING
ON KOBX SIDE)
8 HOLES
Ø.41
4.50
4.50
.50
5.50
3.50
6.50
11.85
7.12
4.73
2.04
45°
45°
9.23
4.50
4.44
LEAD
HOLE
Ø1.09
4 HOLES
.50-13 TAP
ON Ø7.25
B.C.
3.75
3.75
5.72
4.31
8.62
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: C
VERSION: 03
REVISED: 09:07:25 01/19/2023
TDR: 000001201906
MODEL NO. 06LYH929
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 182-4TC TENV V*S MASTER VECTOR W/ BEI HS35
06LYH929

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS