

BALDOR-RELIANCE®

## IEEE 841 motor line

Designed for severe duty applications  
in the most demanding industries

**BALDOR • RELIANCE**



# Certified solutions for severe duty applications

When you specify a Baldor-Reliance IEEE 841 motor, you can trust that it meets the IEEE 841 - 2021 standard to the letter.

All our IEEE 841 rated motors come standard with a PLS® (Positive Lubrication System) bearing lubrication system, inverter-ready nameplate and ship with an IEEE 841 test report. All designs meet the efficiency requirements for North America and are backed by a 5-year warranty.

Every IEEE 841 comes with an embossed, stainless steel nameplate.

**BALDOR • RELIANCE**  
*SuperE* SEVERE DUTY 841XL  
 BALDOR ELECTRIC CO. • FT. SMITH, AR. MFG. IN U.S.A.

CAT. NO. 841XL	CUST. P/N	ENCL. IEEE 841
SPEC. M10000000000	CC 9400	FRAME 2300
SER. NO.	CLASS F	HZ 60
HP 30	ODE BRG 0344	DE BRG 0344
R.P.M. 1725	PH. 3	DES. 0
VOLTS 480	CODE C	ASMA CODE BRG 0000000000
AMPS 33	MOTOR WT. 220 LBS	LUBRICATOR 100L 0000000000
RATING 30/40/50/60/75/90/110	MAX. KVAR 75	
NEMA NOM. EFF. 90.0	NO. OF ROTOR BARS 48	SER. F. 100
GUAR. MIN. EFF. 88.0	NO. OF STATOR BARS 48	P.F. 85
CLASS I DIV. 2 GROUPS A,B,C,D	TEMP. CODE T100	INVERTER POWER 1.0 S.F. ON
CLASS I ZONE 2 GROUPS A,B,C,D	TEMP. °C 100	CHP 00
SPACE HEATERS	LEADS H1-H2	CT 1
VOLTS	AMPS	WATTS
TIE LIKE NUMBERS TOGETHER		
MAX. SPACE HEATER TEMP. °C VT		

Complies with IEEE Std 841-2021

Annotations:  
 - Class I, Division 2 Groups A, B, C, D  
 - IEEE 841-2021  
 - IEEE 45 Marine duty  
 - Certifications (NEMA, UL, IEC)  
 - Inverter duty capabilities

Other certifications:



# IEEE 841 motors

Designed for severe duty applications in the most demanding industries

Our line of 841XL motors are designed to meet and exceed the requirements of IEEE Std. 841. This industry standard was created for the petroleum and chemical industry to improve the reliability, efficiency and performance of severe duty motors used in those applications. Other severe process industries like pulp and paper, cement and mining have also adopted the IEEE 841 standard to help users specify motors for severe duty applications.



IEEE 841XL



IEEE 841XL  
vertical p-base



IEEE 841 / 661XL



## Reliable

The rugged design and extra-tough features of the 841XL minimize vibration, and our patented PLS lubrication system allows the motor to run cooler, providing low-maintenance service in moist, contaminated or harsh environments.



## Easy to install

From oversized conduit boxes, lead separators, colored leads, foot flatness, vertical jack screw holes, dowel pin holes, embossed stainless steel nameplates, this motor has it all.



## Safety

From ease of installation to safe and reliable operation, these motors are certified to be used in hazardous locations (Class I, Division 2).



## Protection

Used in some of the harshest environments, the IEEE 841XL has all the protection a motor needs with premium sealing and IP56 protection.



## Rugged


Heavy-duty cast-iron construction, corrosion resistant epoxy finish and premium efficient electrical designs are backed by a 5-year warranty.



## Globally recognized standards

Baldor-Reliance IEEE 841XL motors exceed the IEEE standard 841 and meet NEMA Premium efficiency standards.


# Baldor-Reliance IEEE 841 motor design for demanding industries



The optional ABB Ability™ Smart Sensor for hazardous locations allows you to remotely monitor the condition of your motor and move from time-based to condition-based maintenance

IP55

IP56



# IEEE 841 specification in demanding industries



Specifications	
<b>Power range</b>	1 thru 500 Hp
<b>Voltage</b>	60Hz 460 and 575 volt (50Hz and other voltages are available)
<b>Mounting</b>	Foot mounted, C-face (foot mounted and footless) and vertical P-base
<b>Ingress protection</b>	IP56 for 841XL and 661XL, IP55 for 841XL vertical P-base (Bearing isolators provide IP66 ingress protection)
<b>Bearings and lubrication</b>	Open bearings and patented PLS lubrication system for bearing longevity
<b>Sealing</b>	Non-contact, rotating labyrinth seal – DE & ODE
<b>Mechanical design</b>	Durable cast-iron end-shields are machined to close tolerances for exacting alignment of bearings and rotor
	All hardware is hex head, high strength and corrosion resistant SAE
	Vertical jacking provisions. NEMA 250 frame and above
	Dowel pin holes. NEMA 250 frame and above
	Grounding: drilled and tapped in frame and ground lug in terminal box
<b>Electrical design</b>	Grease inlet and auto relief fittings
	All frame sizes come standard with an epoxy protection against tropical environments
	Inverter ready per NEMA MG1 Part 31.4.4.2
	Class F insulation with Class B rise @1.0 service factor on sine wave power
<b>Certification and tests</b>	NEMA Design B
	Lead lugs
	Class I, Division 2, Groups A, B, C, D with T3
	Meets and exceeds IEEE Std. 841-2021
	Meets and exceeds IEEE 45 on nameplate
	Complies with JIP33 requirements
<b>Other IEEE 841 requirements</b>	Documented final motor test – ships with motor
	Epoxy paint system exceeds 300+ hour salt fog test per ASTM B117
	Foot flatness within 0.005 inches for precision alignment to driven equipment
	Draft angle on top of mounting feet is 1.5° or less to make proper mounting easier
	Low noise
<b>Only from ABB</b>	Vibration limits 0.08 in/s peak velocity or less
	All internal rotor, stator and shaft surfaces are epoxy coated
	Embossed stainless steel nameplates include all required NEMA data plus actual motor weight and guaranteed minimum efficiency
	5-year warranty
	Optional ABB Ability smart sensor for condition monitoring
	Designed and built in the USA

Red text = specifications exceed IEEE 841-2021 requirements

ABB offers custom Baldor-Reliance IEEE motor designs to meet your performance needs. Contact your local ABB sales office for more information.

# Features that matter

## to extend motor performance



**Exclusive PLS** (Positive Lubrication System) is a patented bearing lubrication design that was developed 40 years ago to ensure proper bearing lubrication in all mounting configurations. Grease is channeled directly into the rolling elements. Easily accessible lubrication fittings are positioned on both endplates and come standard on all Baldor-Reliance IEEE 841 motors.

PLS design allows the bearings to run 5-7°C cooler.

### **Bearing Isolator**

- Provides permanent IP66-rated protection against contamination ingress.
- Contamination chamber collects contaminants trying to enter the bearing housing and expels them through the expulsion port through centrifugal force and gravity.
- Blocks the transfer of vapor contamination created by heating/cooling of the bearing enclosure.

### **Lead segregating gaskets**

Colored leads (up to 320 frame), which are permanently labeled and numbered, provide two-factor identification for easier and safer connections.



Scan to see how it works

---

# IEEE 841XL

## Exceeding the IEEE standard

Our line of 841XL motors are designed to meet or exceed the requirements of IEEE Std. 841-2021. This industry standard was created for the petroleum and chemical industry to improve the reliability, efficiency and performance of severe duty motors used in those applications. Other severe process industries like forest products have also adopted the use of the IEEE 841 standard as it helps promote uniform motor specification and reduce total cost of ownership.


### Typical industries:

- Oil & gas
- Petroleum and chemical
- Pulp & paper
- Metals & foundries
- Cement, aggregate and above ground mining



### Common applications:

- Compressors
- Pumps
- Fans
- Conveyors



# IEEE 841XL vertical P-base

## Pumping applications requiring IEEE performance

The P-base vertical motor, designed to provide outstanding performance, reliability and ease of maintenance, is the most cost effective solution for applications in wastewater; chemical; oil and gas; and pulp and paper applications. The features of IEEE 841XL motors make them an excellent choice for any application that would benefit from longer service life and reduced maintenance. They have been designed to suit your vertical turbine pump needs and provide years of uninterrupted service.

Both medium and high thrust load requirements are available from stock. (Medium thrust LP, High thrust VP)

#### Available custom options:

- API 610 compliant construction
- Non-stock Hp and speeds
- Bearing isolation
- Custom shaft
- Custom mounting face
- Anti-rotation ratchet

#### Typical industries:

- Oil & gas
- Petroleum and chemical
- Wastewater
- Mining
- Pulp and paper
- Other harsh duty environments

#### Common applications:

- Vertical turbine pump



# IEEE 661XL

## Belt-driven, air-cooled heat exchanger motors

Baldor-Reliance 661XL was specifically designed to meet the belt-driven, air cooled heat exchanger specifications of API Standard 661 in vertical mounting configurations. These motors are used in petrochemical facilities to cool process fluids.

661XL meets and exceeds all the requirements of IEEE Std. 841-2021 and the motor requirements of API 661 including 40,000 hr  $L_{10}$  life for belted applications. We take it one step further with enhanced features such as our patented PLS bearing lubrication system, IP56 enclosure that includes dome shaft slinger, anti-condensation auto-drains, drilled and tapped shaft with vertical lifting provisions, bronze labyrinth shaft seal, and gasketed conduit box and cover. All motors are inverter-ready and ship with an IEEE 841 test report.

**Typical industries:**

- Oil & gas
- Petroleum and chemical

**Common applications:**

- Belt drive, ACHE (air cooled heat exchanger)



# ABB Ability condition monitoring

## For hazardous locations

The ABB Ability Smart Sensor for hazardous areas monitors the health and performance of rotating machines operating in hazardous locations.

### Predictive maintenance for motors:

In the past, permanently installed condition monitoring was too expensive to use with the majority of motors. As a result, most of the motors were run until they failed. ABB's cost-effective solution changes all that. With payback time estimated at less than one year, Smart Sensor brings wireless, remote condition monitoring to a much wider range of motors – plants can even implement condition monitoring for entire motor fleets. Condition monitoring means that maintenance activities can be planned in advance, which reduces downtime and supports longer motor life.

### Certified for hazardous areas

The Smart Sensor's enclosure withstands high vibration levels, protects the sensor from dust and water ingress and is rated IP67. The sensor is certified for ATEX, IECEx and NEC500, making it compliant with the strictest requirements for equipment operating in hazardous locations.



(For more information on ABB Ability smart sensors)



### Health checks

ABB's advanced algorithms are used to analyze the data and produce meaningful information such as temperature, vibration, load, number of starts and more. The sensor sends this information directly to a smartphone, gateway, or dedicated portal. Data is also tracked over time for trend analysis.





---

**ABB Motors and Mechanical Inc.**

5711 R.S. Boreham, Jr. Street  
Fort Smith, AR 72901  
Ph: 1.479.646.4711

[new.abb.com/motors-generators](http://new.abb.com/motors-generators)



9AKK108321 EN 08.2021 Printshop 2,000